


HET400PA series

Dimension drawing



UNIT:MM

Features

- ◆ IP55 waterproof at external side
- ◆ FAN / TEC / Control fail alarm
- ◆ Clear LED status indicator
- ◆ High efficiency and reliable fan modules

Design

- ◆ High efficiency of cooling & Heating
- ◆ Thermal electric cooling module
- ◆ Rated voltage at 48V
- ◆ Built-in controller

Main feature	Unit	Specification
Dimension (H x W x D)	mm	210 x 450 x 228
Cooling Capacity ($\Delta T = 0 \text{ } ^\circ\text{C}$)	W	350
Rated voltage	Vdc	48 (TYP.)
Operating voltage range	Vdc	40 ~ 56
Rated current	A	13.5
Power consumption	W	648
Operating temperature range	$^\circ\text{C}$	-40 ~ +55
Weight	Kg	11.0

* Specifications are subject to change without notice.