



Delta Fishing Light

A Revolutionary Light for Fishing

- Saves on Costs
- Enhances Catch Yields
- Withstands Harsh Conditions
- Safer and Healthier



LED is the future trend for fishing

Specific optical design for fishing

LED fixture vs. Traditional HID lamp, LED direct light is more efficient


LED fixture

100%
directed light to the sea






Traditional HID lamp

360° light output, only
30% is directed light to the sea



Fixture tier angle is adjustable, various beam angle choices



1.5 year payback period

LED fishing light cost savings up to 70%

unit: NTD/year

LED 700W replaces HID 2000W

Fixture cost savings
\$1,500,000


3-year fuel cost savings
\$3,804,000

LED 1200W replaces HID 4000W

Fixture cost savings
\$5,200,000


3-year fuel cost savings
\$19,846,857

LED fishing light cost savings up to 70%



Health and Safety

No high temperature burns, UV free prevents skin and eye damage



Advantages of LED fishing lights

Specific LED spectrum to enhance catch yields

Professional optical design, Special spectrum for saury and squid


Enhances catch yields



Saury



Squid



Specific LED spectrum to enhance catch yields

Passed North America ANSIC136 lighting fixture vibration test

Protects against mechanical impacts IK10 Anti-glass explosion

Protects against dust and water - IP66



Delta world class quality products

World No.1 power solution provider

Switches right on

Patented dissipation fan
Easy installation, Ultra light weight



High performance



High quality




Innovative air cooling system, protects against heavy sea waves and anti-salt erosion



100 hrs




148 hrs




Installation cases

Kaohsiung Man Shuen Fa - squid lights




Shantung - squid lights



Kaohsiung Jia Long - saury lights



Kaohsiung Zi Da Wang - squid lights




Kaohsiung Jia Long - saury lights





Bali - squid lights



Specifications

	Model name	FLSF600XXXXFT		
	Input voltage	220 Vac (+/-15%)		
	Output lumen (lm)	60,000	66,000	57,000
	Efficiency (lm/W)	100	110	95
	Wattage (W)	600		
	CCT (K)	2,700	6,100	6,100
	Ra	80	80	90
	Beam angle (°)	100D (70D, 40D optional)		
	Operation (°C)	-20 ~ +45		
	IP	IP66		
	Dimensions (mm)	320(L) x 180(W) x 290(H)		
	Weight (Kg)	6.5		

	Model name	FLSFA12R2D1FT		
	Input voltage	220 Vac (+/-15%)		
	Output lumen (lm)	53,000		
	Wattage (W)	1,200		
	LED color	RED, 620nm		
	Beam angle (°)	120		
	Operation (°C)	-20 ~ +45		
	IP	IP66		
	Dimensions (mm)	431(L) x 415(W) x 343(H)		
	Weight (Kg)	11.4		

	Model name	FLSFA12xx45FT		
	Input voltage	220 Vac (+/-15%)		
	Output lumen (lm)	120,000		
	Efficiency (lm/W)	100		
	Wattage (W)	1,200		
	LED color (K)	5,000		
	Ra	80		
	Beam angle (°)	45		
	Operation (°C)	-20 ~ +45		
	IP	IP66		
	Dimensions (mm)	431(L) x 415(W) x 343(H)		
	Weight (Kg)	11.4		

Global Operations

- Main Sales Offices
- Main Plant Sites
- Main R&D Centers



169 Global Sales Offices

38 Global Plant Sites

64 Global R&D Centers



186 Ruey Kuang Road, Neihu, Taipei 11491, Taiwan, R.O.C.
 TEL : +886 2 8797 2088
 FAX : +886 2 6606 3308
 Email: LT.Sales@deltaww.com



Delta fishing light video