Delta InfraSuite Power Management

Static Transfer Switch

Highly reliable power redundancy for mission critical IT equipment

The Static Transfer Switch (STS) safeguards the uninterrupted operation of mission critical IT equipment. Powered by two independent power sources, the STS rapidly switches from one source to the other automatically when the power supply used to power its connected load fails. For datacenter applications the STS allows power drop risk to be shared or distributed to each rack to prevent power loss for the whole system. The STS offers an efficient and reliable switch that supports the high redundancy requirements of mission critical power systems.

Availability

- Adopts SCR with a relay in parallel as a switching device to increase reliability without sacrificing efficiency.
- Supports power redundant configurations for high reliability
- Monitors the health of the power source and performs the transfer automatically

Convenience

- Rack-mounted type with 1U size for easy installation and relocation
- Built-in SNMP for remote management
- LED indicators show power flow
- Self-test function

Safety

• Break before make prevents short circuits between two sources



▲ Supports power redundant configurations for high reliability



Delta InfraSuite Power Management

Static Transfer Switch

Technical Specifications

Model	STS16002SR	STS30002SR
Rated Current	16A	30A*
Regulatory	CE / UL	CE
Nominal Voltage	200/208/220/230/240 Vac	200/208/220/230/240 Vac
Display	LED	LED
Connection	Input: C20 * 2 pcs	Input : IEC309 / Hardwired
	Output : C13 * 4 + C19 * 1 pcs	Output : IEC309 / Hardwired
Communication	SNMP	SNMP
Operating temperature	0~40°C	0~40°C
Typical Transfer Time	6~10ms	6~10ms
Storage temperature	-15~50°C	-15~50°C
Humidity	0%~95% RH (non-condensing)	0%~95% RH (non-condensing)
Audible Noise (at one meter)	<40dB	<40dB
Physical Dimensions (H x W x D)	43mm x 440mm x 385mm	43mm x 440mm x 385mm / 43mm x 440mm x 390mm
Weight	4.85 Kg	7.6 Kg / 6.2 Kg

^{*} Under the condition of 35 °C; if the environment temperature is $36\sim40$ °C, the product should be de-rated to 25.6A. All specifications are subject to change without prior notice.

STS 16A Front Rear Rear



2007~ 2008 Forbes Asia's Fabulous 50



2009 Frost & Sullivan Green Excellence Award for Corporate Leadership



Delta's Manufacturing System is Certified by ISO 9001 and ISO 14001 Standards



IECQ Certificate of Hazardous Substance Process Management





