



Arcus

Industrial LED High Bay

Product Features

- High system wattage up to 150W (120 lm/W)
- Convenient installation with options for hook hang and wall mount
- Special design allowing joining the light units
- Lens with 30x70°/60x90°/96x152° beam angle for excellent light distribution
- IP65 dust & waterproof protection rate
- Power Factor Control (PFC) function built-in the fixture
- Automatic over-load, over-temperature and over-voltage protection
- Stable product performance due to special heatsink design
- Reliable quality, manufacture capability, and global logistics by Delta Group 45-year establishment

Applications



Commercial



Warehouse






Transport



Industrial

www.delta-emea.com

 **DELTA**
Smarter. Greener. Together.

	D04LHC26xx	D04LHC39xx	D04LHC41xx	D04LHC51xx
Type of product	Industrial Application			
Lumen Output (lm)	7200	10800	14400	18000
Input Voltage (V)	AC 100 / 277 V			
Power (W)	60	90	120	150
Product variation	Clear cover			
CRI (Ra)	>70			
CCT (K)	4000 (Other CCT Available: 3000K, 5000K, 6500K)			
Power Factor	>0.93			
Operating Temp (°C)	-30° C / +50° C			
Product Dimension (mm)	97 x 600	97 x 900	97 x 1200	97 x 1500
Installation Height	6 - 12 m			
Weight (kg)	5	7	9	11
Lifetime	50.000 hr / L70 / 5 years warranty			
Certifications	IP65 / CE / RoHS			
Beam Angle	30x70° / 60x90° / 96x152°			
Dimensions (mm)				
Photometry	 			
14981 lm 60x90°				

Specifications are subject to change without notice.

2016 ver.EN-1.1

Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

