



Athor

Architectural LED Troffer

Product Features

- High system efficacy up to 104 lm/W
- High quality of light in 4000K CRI 80 (3-steps MacAdam)
- UGR <19 luminaire ideal for interior lighting
- Using advanced LED modules with integrated thermal management and optical system
- Unique optical design with microprismatic diffuser
- Innovative LED unit for excellent light quality
- Versions available for 600x600 mm and 625x625 mm ceilings
- Reliable quality, manufacture capability and global logistics by Delta Group 45-year establishment

Applications



Offices



Commercial



Library


www.delta-emea.com



Smarter. Greener. Together.

	D02DECXx330	D02DECXx340	D02DECXx330	D02DECXx340
Type of Product	Office Lighting Solution			
Lumen Output (lm)	3450	3650	3450	3650
Input Voltage (V)	AC 220 / 240 V			
Power (W)	35	35	35	35
Efficacy (lm/W)	99	104	99	104
CRI (Ra)	> 80 (CRI >90 on request)			
CCT (K)	3000	4000	3000	4000
Power Factor	>0.90			
Operating Temp (°C)	-20° C / +35° C			
Options	1-10 V / DALI / 3h Emergency			
Lifetime	50.000 hr / L 80			
Warranty	5 Years			
Conformity	IEC Class I			
Protection	IP20 on the housing / IP40 on the optical part			
Dimensions	595 x 595		295 x 1195	
Dimensions on request	622 x 622		310 x 1245	
Mounting options	Recessed / Surfaced / Suspended			
Accessories optional	Suspension rope 4pcs x 1.35 m (other lengths available on request)			
Weight (kg)	8		8	
Dimensions (mm)				
Photometry	<p>3650 lm 4000 K UGR <19</p>			

Specifications are subject to change without notice.



Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

