

PL01S/D Series

1W DC/DC CONVERTER, SIP-Package, Wide 2:1 Input Range



















FEATURES

- Efficiency up to 80%
- Wide 2:1 Input Range
- Fully regulated Outputs
- Operating Temperature Range -40°C to +85°C
- Low Ripple and Noise
- Isolation Voltage 1500VDC
- Short-circuit Protection
- Lead free, RoHs Compliant
- 3 Years Product Warranty

The PL01S/D series are miniature, SIP Package, isolated 1W DC/DC converters with 1,500VDC isolation. It offers continuous short circuit protection and allows a wide operating temperature range of -40°C to +85°C. These isolated DC/DC converters are the latest offering from a world leader in power systems technology and manufacturing — Delta Electronics, Inc

Model List								
Model	Input	Output	Output Current	Input Current		Max. capacitive	Reflected	Efficiency
Number	Voltage	Voltage				Load	Ripple	(typ.)
	(Range)		Max.	@Max. Load	@No Load		current	@Max. Load
	VDC	VDC	mA	mA(typ.)	mA(typ.)	μF	mA (typ.)	%
PL01S0505A		5	200	263		1680	80	76
PL01S0512A	_	12	83	259		820		77
PL01S0515A	5 (4.5 ~ 9)	15	67	254	40	680		79
PL01D0512A	(4.5 ~ 9)	±12	±42	262		470*		77
PL01D0515A		±15	±33	254		330*		78
PL01S1205A		5	200	108		1680	40	77
PL01S1212A	12 (9 ~ 18)	12	83	108	20	820		77
PL01S1215A		15	67	105		680		80
PL01D1212A		±12	±42	106		470*		79
PL01D1215A		±15	±33	106		330*		78
PL01S2405A		5	200	54		1680		77
PL01S2412A	0.4	12	83	52		820		80
PL01S2415A	24 (18 ~ 36)	15	67	52	10	680	30	80
PL01D2412A	(16 ~ 36)	±12	±42	53		470*		80
PL01D2415A		±15	±33	52		330*		80
PL01S4805A		5	200	27		1680		77
PL01S4812A	10	12	83	27		820		78
PL01S4815A	48 (36 ~ 75)	15	67	27	7	680	20	78
PL01D4812A	(30 ~ 73)	±12	±42	27		470*		79
PL01D4815A		±15	±33	26		3308		79

^{*} For each output



input Characteristics						
Parameter	Model	Min.	Тур.	Max.	Unit	
	5V Input Models	-0.7		15		
Innut Curre Valtana (4 ana mary)	12V Input Models	-0.7		25		
Input Surge Voltage (1 sec. max.)	24V Input Models	-0.7		50		
	48V Input Models	-0.7		100	\/D0	
	5V Input Models			4.5	VDC	
Otant Ha Thurshald Value	12V Input Models			9		
Start-Up Threshold Voltage	24V Input Models			18		
	48V Input Models			36		
Internal Filter Type	All Models	Capacitor				


Parameter	Con	nditions	Min.	Тур.	Max.	Unit
Output Voltage Setting Accuracy	At 50% Load	and Nominal Vin			±1.0	%Vnom
Line Regulation	Vin=Mi	n. to Max.			±0.2	%
	No Load to Full Load 10% to 90% Load	Single Output Models			±1.0	%
Load Damilation		Dual Output Models			±1.0	%
Load Regulation		Single Output Models			±0.5	%
		Dual Output Models			±0.8	%
Min.Load	No minimum Load Requirement					
Ripple & Noise (20MHz)				50		mV _{P-P}
Transient Recovery Time	25% Load Step Change			250		µsec
Temperature Coefficient					±0.02	%/°C
Short Circuit Protection	Continuous					

General Characteristics							
Parameter	Conditions	Min.	Тур.	Max.	Unit		
I/O Isolation Voltage (rated)	60 Seconds	1500			VDC		
I/O Isolation Resistance	500 VDC	1000			ΜΩ		
I/O Isolation Capacitance	100KHz, 1V			50	pF		
Switching Frequency			250		KHz		
MTBF(calculated)	MIL-HDBK-217F@25°C, Ground Benign	2,800,000			Hours		

Environmental Characteristics						
Parameter	Conditions	Min.	Max.	Unit		
Operating Ambient Temperature Range (See Power	Natural Convection	-40	+85	°C		
Derating Curve)						
Case Temperature			+105	°C		
Storage Temperature		-55	+125	°C		
Humidity (non condensing)			95	% rel. H		
Lead Temperature (1.5mm from case for 10Sec.)			260	℃		








Notes

- 1 Specifications typical at Ta=+25°C, resistive load, nominal input voltage, rated output current unless otherwise noted.
- 2 Ripple & Noise measurement bandwidth is 0-20 MHz.
- 3 All DC/DC converters should be externally fused at the front end for protection.
- 4 That "natural convection" is about 20LFM but is not equal to still air (0 LFM).
- 5 Specifications subject to change without notice.

Mechancial Drawing



Pin Connections						
Pin	Single Output	Dual Output				
1	-Vin	-Vin				
2	+Vin	+Vin				
4	+Vout +Vout					
5	No Pin	Common				
6	-Vout	-Vout				

- ► All dimensions in mm (inches)
- ► Tolerance: X.X±0.5 (X.XX±0.02)

X.XX±0.25 (X.XXX±0.01)

Pins ±0.05(±0.002)

Physical Outline

Case Size : 17.0x7.62x11.0mm (0.67x0.30x0.43 inches)

Case Material : Non-Conductive Black Plastic (flammability to UL 94V-0 rated)

Pin Material : Alloy 42

Weight : 12.9g



Part Numbering System							
Р	L	01	S	05	05	A	
Form factor	Family series	Watt	Number of Outputs	Input Voltage	Output Voltage	Option Code	
D-DIP	A~Z	01:1W	S - Single	03:3.3V	03:3.3V	A - Std. Functions	
P-SIP		02:2W	D- Dual	05: 5V	05: 5V		
S-SMD		03:3W		12:12V	12:12V		
		04:4W		24: 24V	15: 15V		
		06:6W		48:48V	24: 24V		

WARRANTY

Delta offers a three(3) years limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.