








DELTA P/N: TLM106012F Series

Mechanical Dimensions & Schematic



Suggested PWB Layout

UNIT : mm
 A = 10.0 MAX
 B = 6.0 MAX
 C = 12.0 MAX
 D = 0.85
 E = 1.1
 F = 3.0
 G = 2.3
 H = 8.35
 I = 1.35
 J = 1.9
 K = 3.5
 L = 3.55
 M = 10.05



Electrical Characteristics @ 25°C, 100kHz, 1V

Delta P/N	L (nH) ± 15%	Li (nH) MIN	DCR (mΩ) ± 10%		Isat ¹ (A)			Ir ² (A)	Ir ² (A)
			1-4	2-3	25°C	100°C	125°C		
TLM106012F-101	100	70			109	93	87		
TLM106012F-121	120	84	0.16	0.38	88	75	70	68	35
TLM106012F-151	150	105			69	59	55		

1. Isat is the DC current which causes the inductance drop to Li
2. Ir is the DC current which causes the surface temperature of the part increase approximately 40 °C.
3. Operating temperature: -40°C to 125°C (Self-temperature rise included).