


MH092D3RD



IST ELP-06V or equivalent

• Housing: JST ELP-06V or equivalent

Pin 1: Red, Vm (310 VDC)

Pin 2: Empty

Pin 3: White, Vcc (15 VDC)

Pin 4: Blue, F/G Signal Output (4 pulses/rev.)

Pin 5: Yellow, Vsp (0 ~ 5.7 VDC)

Pin 6: Black, GND)

· Safety: CCC

A-A View

Model No.	Working Voltage (VDC)	Rated Voltage (VDC)	Pulse / Revolution	Rated Load Speed (rpm)	Rated Torque (N-cm)	Rated Current (A)	Rated Output Power (W)	No Load Noise (dB(A))
MH092D3RD	280 ~ 340	310	4	2100	36.4	0.370	80	< 50

Unit: mm

- Noise measuring condition: shaft horizontal / mic. 15 cm away from motor
- All readings are typical values at rated voltage.
- Specifications are subject to change without notice.