



Internal door mount

Features


- ♦ IP55 waterproof at external side
- ♦ Dry contact alarm output

Design

- ♦ Air to air heat exchange
- Rated voltage at 24V
- Reduntant fan quantity design
- High efficiency and reliable fan
- Easy installation and maintenance

HEX020VA series

Dimension drawing



Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	590 x 283 x 99 (23 x 11 x 4)
Cooling capacity _{*Note}	W/K (W/° F)	20 (11)
Rated voltage	VDC	24
Operating current	Α	0.9
Opearting power	w	22
Operating voltage range	VDC	20 - 26
Operating temperature range	°C	-10 ~ +65
Noise (1.5 meter)	dB-A	54.0
Weight	Kg (Lb)	7 (15)

* Note : The cooling capacity (W/K , W/°C or W/°F) is defined as $Q/(T_I-T_A)$

Q : Heat dissipation (W) from inside of cabinet

 $T_{I}:$ Return temperature of internal air circuit (K , °C or °F)

- T_A : Ambient temperature of external air circuit (K , °C or °F)
- * Specifications are subject to change without notice.