




Roof mount



HEX050QA series

Dimension drawing



EXTERNAL OUTLET

Main feature	Unit	Specification
Dimension (W x D x H)	mm (in)	550 x 434 x 155 (22 x 17 x 6)
Cooling capacity _{*Note}	W/K (W/° F)	50 (28)
Rated voltage	VDC	48
Operating current	Α	1.4
Opearting power	w	68
Operating voltage range	VDC	40 ~ 60
Operating temperature range	°C	-10 ~ +65
Noise (1.5 meter)	dB-A	64.0
Weight	Kg (Lb)	9 (20)

* Note : The cooling capacity (W/K , W/°C or W/°F) is defined as Q/ (TI-TA)

Q : Heat dissipation (W) from inside of cabinet

TI : Return temperature of internal air circuit (K , °C or °F)

- TA : Ambient temperature of external air circuit (K , °C or °F)
- * Specifications are subject to change without notice.

Features

- IP55 waterproof at external side
- One touch" dry run test and dust cleaning
- ♦ Standalone temperature control
- Clear LED status indicator
- Dry contact alarm output

Design

- ♦ Air to air heat exchange
- Rated voltage at 48V
- Reduntant fan quantity design
- High efficiency and reliable fan
- Easy installation and maintenance