

Door Mounting type



Features


- ♦ IP55 waterproof at external side
- ◆ "One touch" dry run test and dust cleaning
- Standalone temperature control
- ◆ Clear LED status indicator
- ◆ Dry contact alarm output

Design

- ♦ Air to air heat exchange
- ◆ Rated voltage at 48V
- Reduntant fan quantity design
- ♦ High efficiency and reliable fan
- ◆ Easy installation and maintenance

HEX250PA series

Dimension drawing



Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	1198 x 738 x 350 (47.1 x 29 x 13.8)
Cooling capacity _{*Note}	W/K (W/F)	250 (139)
Rated voltage	Vdc	48 (TYP.)
Operating voltage range	Vdc	40 - 60
Rated current	Α	12 max.
Power consumption	W	480 max.
Operating temperature range	c	-20 ~ +65
Internal airflow	CFM	600
External airflow	CFM	650
1.5M sound pressure noise	dB-A	68.0
Weight	Kg	60.0

^{*} Note : The cooling capacity (W/K OR W/C) is defined as Q/ (T_{\(\tilde{\}\)}T_{\(\text{A}\)}

Q: Heat dissipation (W) from inside of cabinet

 \textbf{T}_{I} : Return temperature of internal air circuit (K OR $\textbf{\^{C}})$

 T_A : Ambient temperature of external air circuit (K OR $^{\circ}$ C)