





Common Chokes


EMI Common-Mode Suppression Inductors

LFO20V Type

Mechanical Dimension: Unit: mm



Schematic :



Electrical Characteristics:

■ AT 25°C, 40KHz/1V Tested:

PART NO.	INDUCTANCE (mH) MIN	DCR (mΩ) MAX	RATED CURRENT (Aac)	TEMPERATURE RISE (°C) MAX
LFO20V01	33.0	2870	0.30	45
LFO20V02	22.0	1890	0.40	45
LFO20V03	16.0	1400	0.50	45
LFO20V04	13.0	1110	0.55	45
LFO20V05	10.5	990	0.60	45
LFO20V06	9.0	745	0.70	45
LFO20V07	7.0	580	0.80	45
LFO20V08	5.0	410	0.90	45
LFO20V09	4.0	330	1.10	45
LFO20V10	3.0	255	1.30	45
LFO20V11	1.8	155	1.70	45
LFO20V12	1.2	105	2.00	45

* WITHSTANDING VOLTAGE BETWEEN L1 & L2 1.5KV 1 MINUTE
* GOOD DIFFERENCE IN WINDING L1 & L2 INDUCTANCE



DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 252, SAN YING ROAD, KUEISAN INDUSTRIAL ZONE, TAOYUAN SHIEN, 333, TAIWAN, R.O.C.

TEL: 886-3-3591968; FAX: 886-3-3591991

<http://www.deltaww.com>