

1 Electronic Design Spec

1.1. INPUT VOLTAGE

Rated input voltage: 100-240VAC

Input voltage range: 90-264VAC

Rated input frequency: 50-60Hz

Input frequency range: 47-63Hz

1.2. CONSTANT VOLTAGE

The constant voltage is 42V (252W)

The accuracy has to be +/- 0.2V.


1.3. CONSTANT CURRENT

The constant current is 6A.

The accuracy has to be +/- 0.2A.

1.4. Charge curve

□ Charge Curve



台達電子工業股份有限公司
DELTA ELECTRONICS, INC.

DESCRIPTION :
電氣規格 (Electrical Specification)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DELTA ELECTRONICS, INC. AND SHALL NOT BE REPRODUCED OR USED AS THE BASIS FOR THE MANUFACTURE OR SELL OF APPARATUSES OR DEVICES WITHOUT PERMISSION.

MODEL NO. :

ADP-252W

Date	Drawn	Design (EE)	Design (ME)	DOCUMENT NAME. :	REV.
2020/02/11		Chieh	Mingche	ES-252W	S00

File Name:

SHEET 2 OF 6

1.5. STATUS INDICATION (LED)

A visual indicator (LED for instance) must inform of the following status:

When PSU is stand-by mode: Green steady

When PSU is pre-charge mode: Red blinking

When PSU is charge mode: Red steady

When PSU is fully charge mode: Green steady

When PSU is over timing mode: Green 1sec/ Red 1sec blinking

When PSU is protect mode: LED off.

1.6. Harmonic

Class D

1.7. ALTITUDE

3000m

1.8. Inrush current

No damage.

1.9. Acoustic Noise

At 1 meter the noise must be < 35dB

2. CERTIFICATIONS (Safety / EMC)

The charger has to comply with regulation, standard and laws and pass every Safety and EMC certifications.

Certification: The charger has to be UL1012 and IEC/EN60335-2-29

2.1. Lightning surge immunity:


Follow the norm of IEC-61000-4-5 requirements

Line to Line: 1kV 50us 5 time performance Criterion B

2.2. Electric Fast transients (EFT):

Follow the norm of IEC-61000-4-4 requirements

IEC61000-4-4 level 3 (2kV), performance Criterion B

 台達電子工業股份有限公司 DELTA ELECTRONICS, INC.				DESCRIPTION : 電氣規格 (Electrical Specification)	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DELTA ELECTRONICS, INC. AND SHALL NOT BE REPRODUCED OR USED AS THE BASIS FOR THE MANUFACTURE OR SELL OF APPARATUSES OR DEVICES WITHOUT PERMISSION.				MODEL NO. : ADP-252W	
Date	Drawn	Design (EE)	Design (ME)	DOCUMENT NAME. :	REV.
2020/02/11		Chieh	Mingche	ES-252W	S00

File Name:

SHEET 3 OF 6

2.3. Electrostatic Discharge (ESD):

Follow the norm of IEC-61000-4-2 requirements

- (1). +/-8KV air discharge performance Criterion B
- (2). +/-6KV contact discharge performance Criterion B

2.4. Voltage Dips/Short Interruption:

Follow the norm of EN61000-4-11 requirements

- (1). Voltage Dips 30% reduction 10ms, performance Criterion B
- (2). Voltage Dips 60% reduction 100ms, performance Criterion C
- (3). Voltage Dips 95% reduction 5000ms, performance Criterion C

2.5. Dielectric Withstand Voltage (HI-POT)

Primary to Secondary: 3000Vac, 10mAmax for 1 minute

2.6. Leakage current

It shall be less than 300uA at 264Vac/60Hz

2.7. Insulation Resistance (IR)

PRIMARY(L,N) to SECONDARY use 500Vdc test ; Insulation resistance limit: >10M ohm


2.8. Electromagnetic interference (EMI)

CISPR 32 Class B

3. PROTECTION

3.1. OVER VOLTAGE PROTECTION

The power supply shall auto-recovery and no damage occurs if the output is over voltage. The output voltage less than 45V.

				台達電子工業股份有限公司 DELTA ELECTRONICS, INC.		DESCRIPTION : 電氣規格 (Electrical Specification)	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DELTA ELECTRONICS, INC. AND SHALL NOT BE REPRODUCED OR USED AS THE BASIS FOR THE MANUFACTURE OR SELL OF APPARATUSES OR DEVICES WITHOUT PERMISSION.				MODEL NO. : ADP-252W			
Date	Drawn	Design (EE)	Design (ME)	DOCUMENT NAME. :			REV.
2020/02/11		Chieh	Mingche	ES-252W			S00

3.2. OUTPUT CURRENT PROTECTION

The power supply shall auto-recovery and no damage occurs if the output is over current. The output current shall less than 150% of rated output current.

3.3. OUTPUT SHORT CIRCUIT PROTECTION

The power supply shall auto-recovery and no damage occurs. If the short circuit is applied to the output.

3.4. OVER TEMPERATURE PROTECTION

The power supply shall auto-recovery and no damage occurs if the component temperature is higher than normal work.

3.5. TIMING PROTECTION

When pre-charge mode charging time over 1hour \pm 20min, the charger stops charging and Green 1sec/ Red 1sec blinking.

When charge mode charging time over 9hours \pm 1hour, the charger stops charging and Green 1sec/ Red 1sec blinking.

4. TEMPERATURE

4.1. Operation

4.1.1 Temperature Operating


The AC Adapter shall be capable of operating at full load with an ambient temperature range of 0°C to +40°C.

4.1.2 Temperature Storage

The AC Adapter shall be capable of withstanding ambient temperature from -20°C to +70°C.

4.1.3 Humidity Operating

The AC Adapter shall be capable of operation in relative humidity of 10% to 90%.

 台達電子工業股份有限公司 DELTA ELECTRONICS, INC.				DESCRIPTION : 電氣規格 (Electrical Specification)	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DELTA ELECTRONICS, INC. AND SHALL NOT BE REPRODUCED OR USED AS THE BASIS FOR THE MANUFACTURE OR SELL OF APPARATUSES OR DEVICES WITHOUT PERMISSION.				MODEL NO. : ADP-252W	
Date	Drawn	Design (EE)	Design (ME)	DOCUMENT NAME. :	REV.
2020/02/11		Chieh	Mingche	ES-252W	S00


4.1.4 Humidity Storage

The AC Adapter shall be capable of withstanding ambient relative humidity of 5% to 95%.

5. Reliability requirements

MTBF (standard, environmental temperature, load requirement) ≥ 30 K hour

Testing condition : full load/ 25°C .

				台達電子工業股份有限公司 DELTA ELECTRONICS, INC.		DESCRIPTION : 電氣規格 (Electrical Specification)	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DELTA ELECTRONICS, INC. AND SHALL NOT BE REPRODUCED OR USED AS THE BASIS FOR THE MANUFACTURE OR SELL OF APPARATUSES OR DEVICES WITHOUT PERMISSION.						MODEL NO. : ADP-252W	
Date	Drawn	Design (EE)	Design (ME)	DOCUMENT NAME. :			REV.
2020/02/11		Chieh	Mingche	ES-252W			S00