






- * Bearing Type **Ball Bearings**
- * Material Impeller & Frame: Plastic (UL 94V-0)
- * Lead Wires : UL 1007 AWG #24 OR Equivalent Red Wire Positive(+) Black Wire Negative(-)
- * Weight: 58g (2.05 oz)


BF: 76 x 70 x 20 MM SERIES

■ DIMENSIONS DRAWING



mm UNIT: (INCH)

■ P & Q CURVE (AT RATED VOLTAGE)



MODEL		Rated Voltage	Operating Voltage Range	Input Current	Input Power	Speed	Maximum Air Flow		Maximum Air Pressure		Noise
PART NO.	FUNCTION	VDC	VDC	Amp	Watt	R.P.M.	m³/min	CFM	mmH ₂ O	IN H₂O	dB-A
BFB0712LD	-R00 / -F00	12	7.0 to 13.8	0.13	1.56	2800	0.172	6.07	13.36	0.562	32.5
BFB0712HD	-R00 / -F00	12	7.0 to 13.8	0.31	3.72	4000	0.231	8.52	26.27	1.034	42.0

^{*} The max. air flow and the speed are measured in free air; max. air pressure is measured at zero air flow.

^{*} Noise is measured in anechoic chamber in free air, one meter from intake side.

^{*} All readings are typical values at rated voltage.

* Specifications are subject to change without notice