







- * Bearing Type **Ball Bearings**
- * Material
- Impeller & Frame: Plastic (UL 94V-0)
- * Lead Wires : UL 1007 AWG #24 OR Equivalent Red Wire Positive(+) Black Wire Negative(-)
- * Weight: 140g (4.94 oz)

75 x 80 x 30 MM SERIES

■ DIMENSIONS DRAWING



■ P & Q CURVE (AT RATED VOLTAGE)



MODEL		Rated Voltage	Operating Voltage Range	Input Current	Input Power	Speed	Maximum Air Flow		Maximum Air Pressure		Noise
PART NO.	FUNCTION	VDC	VDC	Amp	Watt	R.P.M.	m³/min	CFM	mmH ₂ O	IN H ₂ O	dB-A
BCB0812EHN	-R00 / -F00	12	6.0 to 13.2	1.00	12.00	8200	0.632	22.32	49.54	1.950	64.0
BCB0812GHN	-R00 / -F00	12	6.0 to 13.2	1.45	17.40	9500	0.736	25.99	67.64	2.663	67.8
BCB0812UHN	-R00 / -F00	12	6.0 to 13.2	2.30	27.60	10800	0.854	30.16	93.35	3.675	69 .3

^{*} Function type is optional.
* The max. air flow and the speed are measured in free air ; max. air pressure is measured at zero air flow.

^{*} Noise is measured in anechoic chamber in free air, one meter from intake side.

^{*} All readings are typical values at rated voltage.

* Specifications are subject to change without notice