


Wall mount

HEC0500BFA series

HEC0500FFA series (with Heater)



Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.
- ◆ Heater function. (optional)

Design

- ◆ Compact size.
- ◆ Rated voltage at 230 VAC.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	550 x 295 x 160 (21.7 x 11.6 x 6.3)
Cooling capacity* _{Note}	W (BTU/hr)	550 (1800)
Rated voltage	VAC	230
Operating power	W	268
Operating voltage range	VAC	196 ~ 264
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	61.0
Weight	Kg (Lb)	16 (35.2)
Heater (optional)	W	300

* Note : L35/L35

* Specifications are subject to change without notice.