




- \* Bearing Type **Ball Bearings**
- Material
- Impeller & Frame : Plastic (UL 94V-0) \* Lead Wires :
- UL 1007 AWG #24 OR Equivalent Red Wire Positive(+) Black Wire Negative(-)
- \* Weight : 176g (6.21 oz)



## DIMENSIONS DRAWING



MODEL		Rated Voltage	Operating Voltage Range	Input Current	Input Power	Speed	Maximum Air Flow		Maximum Air Pressure		Noise
PART NO.	FUNCTION	VDC	VDC	Amp	Watt	R.P.M.	m³ /min	CFM	mmH₂O	IN H <sub>2</sub> O	dB-A
BCB1012EH	-R00 / -F00	12	6.0 to 13.2	1.30	15.60	6700	0.730	25.78	51.77	2.038	63.9
BCB1012GH	-R00 / -F00	12	6.0 to 13.2	2.20	26.40	8000	0.867	30.62	74.71	2.941	67.3
BCB1012UH	-R00 / -F00	12	6.0 to 13.2	3.20	38.40	9300	1.000	35.31	102.95	4.053	67.8

Air Flow

 $\Rightarrow$ 

\* Function type is optional. \* The max. air flow and the speed are measured in free air ; max. air pressure is measured at zero air flow.

\* Noise is measured in anechoic chamber in free air, one meter from intake side.

\* All readings are typical values at rated voltage. \* Specifications are subject to change without notice