


Internal door mount

HEX150PB series

Dimension drawing



Features

- ◆ IP55 waterproof at external side
- ◆ "One touch" dry run test and dust cleaning
- ◆ Standalone temperature control
- ◆ Clear LED status indicator
- ◆ Dry contact alarm output

Design

- ◆ Air to air heat exchange
- ◆ Rated voltage at 48V
- ◆ Redundant fan quantity design
- ◆ High efficiency and reliable fan
- ◆ Easy installation and maintenance

Main feature	Unit	Specification	
Dimension (H x W x D)	mm (inch)	640 x 550 x 278 (25 x 22 x 11)	
Cooling capacity ^{*Note}	W/K (W/°F)	110 (61)	150 (83)
Rated voltage	VDC	48	
Operating current	A	2.6	5.8
Operating power	W	125	279
Operating voltage range	VDC	40 ~ 60	
Operating temperature range	°C	-10 ~ +65	
Noise (1.5 meter)	dB-A	65.0	73.0
Weight	Kg (Lb)	20 (44)	

* Note : The cooling capacity (W/K , W/°C or W/°F) is defined as $Q / (T_I - T_A)$

Q : Heat dissipation (W) from inside of cabinet

T_I : Return temperature of internal air circuit (K , °C or °F)

T_A : Ambient temperature of external air circuit (K , °C or °F)

* Specifications are subject to change without notice.