


Internal door mount



HEX020VB series

Dimension drawing



Features

- ◆ IP54 waterproof at external side
- ◆ Compact size

Design

- ◆ Air to air heat exchanger
- ◆ Rated voltage at 24VDC
- ◆ High efficiency and reliable fan
- ◆ Easy installation and maintenance

| Main feature | Unit | Specification |
|----------------------------|------------|-----------------------------------|
| Dimension (H x W x D) | mm (inch) | 384 x 205 x 95 (15.1 x 8.1 x 3.7) |
| Cooling capacity *Note | W/K (W/°F) | 20 (11) |
| Rated voltage | VDC | 24 |
| Operating current | A | 1.2 |
| Operating power | W | 28.8 |
| Operating voltage range | VDC | 16 - 26.4 |
| Operating temperatur range | °C | -10 ~ +65 |
| Noise (1.5 meter) | dB-A | 65.0 |
| Weight | Kg (Lb) | 4 (8.8) |

*Note : The cooling capacity (W/K, W/°C or W/°F) is defined as $Q/[(T_i+T_s)/2-T_A]$

Q : Heat dissipation (W) from inside of cabinet

T_i : Return temperature of internal air circuit (K, °C or °F)

T_s : Supply temperature of internal air circuit (K, °C or °F)

T_A : Ambient temperature of external air circuit (K, °C or °F)

*Specifications are subject to change without notice.