

Internal door mount



Features


- ◆ IP54 waterproof at external side
- ◆ Compact size

Design

- ◆ Air to air heat exchanger
- ◆ Rated voltage at 100 / 200 VAC
- ◆ High efficiency and reliable fan
- ◆ Easy installation and maintenance

HEX030JB series

Dimension drawing



Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	650 x 300 x 90 (25.6 x 11.8 x 3.5)
Cooling capacity *Note	W/K (W/°F)	30 (16.5)
Rated voltage	VAC	100 / 200
Operating current	A	0.6 / 0.3
Operating power	W	60 / 60
Operating voltage range	VAC	100 - 240
Operating temperatur range	°C	-10 ~ +65
Noise (1.5 meter)	dB-A	55.0
Weight	Kg (Lb)	7 (15.4)

*Note : The cooling capacity (W/K, W/°C or W/°F) is defined as $Q/[(T_i+T_s)/2-T_A]$

Q : Heat dissipation (W) from inside of cabinet

T_i : Return temperature of internal air circuit (K, °C or °F)

T_s : Supply temperature of internal air circuit (K, °C or °F)

T_A : Ambient temperature of external air circuit (K, °C or °F)

*Specifications are subject to change without notice.