


Wall mount

HEC0500XB series

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.

Design

- ◆ Compact size.
- ◆ Rated voltage at 48V.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	545x315x175 (21.4 x 12.4 x 6.9)
Cooling capacity*Note	W (BTU/hr)	500 (1700)
Rated voltage	VDC	48
Operating current	A	11.0
Operating voltage range	VDC	40 ~ 58
Operating temperature range	°C	-40 ~ +55
Noise (1.5 meter)	dB-A	65.0
Weight	Kg (Lb)	13.5 (29.8)

* Note : L35/L35

* Specifications are subject to change without notice.