


Wall mount

HEC0600BAS series

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions
- ◆ Energy efficient fans and effective compressor
- ◆ IP55 waterproof at external side
- ◆ Precise temperature control
- ◆ Earth-friendly refrigerant (GWP <7)
- ◆ Dry contact alarm output
- ◆ Remote control function

Design

- ◆ Compact size
- ◆ Rated voltage at 200 ~ 240 VAC
- ◆ Built-in smart controller
- ◆ High efficiency and reliable fan
- ◆ Easy installation and maintenance

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	500 x 350 x 230 (19.69 x 13.78 x 9.06)
Cooling capacity*Note	W (BTU/hr)	600 (2047)
Rated voltage	VAC	200 ~ 240
Operating current	A	1.3
Operating voltage range	VAC	180 ~ 264
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	60
Weight	Kg (Lb)	18.5 (40.8)

* Note : L35/L35

* Specifications are subject to change without notice.