




Wall mount



HEC0600BFR

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ UL type 4X waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.
- ◆ Remote control function

Design

- ◆ Compact size.
- ◆ Rated voltage at AC230V.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D) (without flange)	mm (inch)	508 x 254 x 254 (20 x 10 x 10)
Cooling capacity*Note	W (BTU/hr)	600 (2049)
Heating	W	NA
Rated voltage	VAC	230
Frequency	HZ	50 / 60
Operating power	W	322
Operating voltage range	VAC	207 ~ 253
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	63.0
Weight	Kg (Lb)	16 (35.3)

* Note : L35/L35, AC230V/60HZ

* Specifications are subject to change without notice.