


Door mount



HEC2500BFE series

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.

Design

- ◆ Compact size.
- ◆ Rated voltage at 230 VAC.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	1092.5 x 399 x 275 (43.0 x 15.7 x 10.8)
Cooling capacity* _{Note}	W (BTU/hr)	2500 (8500)
Rated voltage	VAC	230
Operating power	W	1250
Operating voltage range	VAC	196 ~ 264
Operating temperature range	°C	-10 ~ +55
Noise (1.5 meter)	dB-A	65.0
Weight	Kg (Lb)	40 (88.0)

* Note : L35/L35

* Specifications are subject to change without notice.