



Wall mount



HEC3512FFA series

Dimension drawing



mm [inch]

Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.

Design

- ◆ Compact size.
- ◆ Dual power input:
 - Rated voltage at 48VDC.
 - Rated voltage at 230VAC 50/60Hz.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	1300 x 500 x 250 (51.2 x 19.7 x 9.8)
Cooling capacity*Note	W (BTU/hr)	3500(11943) /50HZ
Rated voltage	VDC VAC	48 230VAC 50/60 Hz
Operating current	A	8.3
Operating voltage range	VDC VAC	40 ~ 58 207 ~ 253
Operating temperature range	°C	-40 ~ +55
Noise (1.5 meter)	dB-A	65.0
Weight	Kg (Lb)	58 (128)

* Note : L35/L35

* Specifications are subject to change without notice.