




Wall mount



HEC2010FFA series

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.
- ◆ Heating function.

Design

- ◆ Compact size.
- ◆ Rated voltage at 230 VAC.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	945 x 505 x 250 (37.2 x 19.9 x 9.8)
Cooling capacity*Note	W (BTU/hr)	2000 (6824)
Rated voltage	VAC/VDC	230/48
Operating power	W(AC/DC)	805/159
Operating voltage range	VAC/VDC	207 ~ 253/40~58
Heating capacity	W (BTU/hr)	1000 (3400)
Operating temperature range	°C	-10 ~ +55
Noise (1.5 meter)	dB-A	65.0
Weight	Kg (Lb)	40 (88)

\* Note : L35/L35

\* Specifications are subject to change without notice.