REVISION : A0

PAGE : 1 OF 7


SPECIFICATION FOR APPROVAL

1. Scope

This specification applies to 1.2mm x 2.0mm size 1/2W, fixed metal film chip resistors rectangular type for use in electronic equipment.

1/2W, 0805 Low Resistance Chip Resistor (Lead / Halogen free)

2. Type Designation



(3) Resistance value: For example— $R005 = 0.005 \Omega$

(4) Resistance tolerance:

$$F= \pm 1\%$$

 $G= \pm 2\%$
 $J= \pm 5\%$

3. Construction and Physical Dimensions




Figure 1. Structure (No mark)

| Code Letter | Dimensions (mm) | |
|-------------|-----------------|--|
| L | 1.3 ± 0.20 | |
| W | 2.0 ± 0.20 | |
| t | 0.50 ± 0.20 | |
| a | 0.35 ± 0.15 | |
| b | 0.35 ± 0.15 | |

NOTE:

- ① Resistive element (under protection film)
- ② Electrode
- 3 Protection film
- 4 Substrate

REVISION : A0

PAGE : 2 OF 7

4. Ratings

4-1 Specification

| Power Rating* | 1/2 W | |
|---------------------------------------|-------------------------------|--|
| Resistance Range | 0.005Ω ~ 0.030Ω | |
| Resistance Tolerance | ±1%, ±2%, ±5% | |
| Temperature Coefficient of Resistance | 0~200ppm/°C | |

Note*:

Power Rating is based on continuous full load operation at rated ambient temperature of 70° C. For resistors operated at ambient temperature in excess of 70° C, the maximum load shall be derated in accordance with the following curve.




Figure 2 Derating Curve

4-2 Rated Voltage

The rated voltage shall be determined by the following expression.

$$V = \sqrt{P \times R}$$
 Where V: Rated voltage (V)

R: Nominal resistance value (Ω)

P: Rated dissipation (W)

4-3 Operating and Storage Temperature Range

REVISION : A0

PAGE : 3 OF 7

5. Characteristics

| Test Item | Condition of Test | Requirements |
|------------------------------|---|--|
| Short Time Overload | 5 * Rated power for 5 seconds Refer to JIS C 5201-1 4.13 | $\Delta R: \pm (0.5\% + 0.0005\Omega)$ Without significant damage by flashover (spark, arching), burning or breakdown etc. |
| Insulation Resistance | The resistor shall be cramped in the metal block and tested , as shown below. Test voltage : $100 \pm 15 V_{DC}$ for 1 minute Refer to JIS C 5201-1 4.6 Mounting condition G. | Between Electrode and Protection Film $100M\Omega$ or over Between Electrode and Substrate $1,000M\Omega$ or over |
| Voltage Proof | The voltage : 100V _{AC} (rms.) for 1 minute Refer to JIS C 5201-1 4.7 | $\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without damage by flashover, fire or breakdown, as shown below. |
| Thermal Shock | -55 ~125°C 5 cycles, 15 min at each extreme condition Refer to JIS C 5201-1 4.19 | $\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance |
| Low Temperature Storage | Kept at -55°C, 1,000 hours Refer to JIS C 5201-1 4.23.4 | $\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance |
| High Temperature Exposure | Kept at 125°C for 1,000 hours Refer to JIS C 5201-1 4.23.2 | $\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance |
| Solderability | Temperature of Solder : $245 \pm 5^{\circ}$ C Immersion Duration : 2 ± 0.5 second Refer to JIS C 5201-1 4.17 | Uniform coating of solder cover minimum of 95% surface being immersed |
| Resistance to Soldering Heat | Dipped into solder at $270 \pm 5^{\circ}$ C for 10 ± 1 seconds Refer to JIS C 5201-1 4.18 | $\Delta R: \pm (0.5\% + 0.0005\Omega)$ Without distinct deformation in appearance |

REVISION : A0


PAGE : 4 OF 7

| Test Item | Condition of Test | Requirements |
|---------------------|---|--|
| Load Life | Rated voltage for 1.5 hours followed by a pause 0.5 hour at $70 \pm 2^{\circ}$ C. Cycle repeated 1000 hours Refer to JIS C 5201-1 4.25 | $\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance |
| Damp Heat with Load | 40 ± 2°C with relative humidity 90% to 95%. D.C. rated voltage for 1.5 hours ON and 30 minutes OFF. Cycle repeated 1,000 hours Refer to JIS C 5201-1 4.24 | $\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance |
| Mechanical Shock | 100 G's for 6milliseconds. 5 pulses Refer to JIS C 5201-1 4.21 | $\begin{split} \Delta R : & \pm (0.5\% + 0.0005 \Omega) \\ & \text{Without mechanical damage such} \\ & \text{as break} \end{split}$ |
| Bending Test | Glass-Epoxy board thickness: 1.6mm Bending width: 2mm Between the fulcrums: 90mm Refer to JIS C 5201-1 4.33 | $\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without mechanical damage such as break |

REVISION: A0

PAGE : 5 OF 7

6. Recommended Solder Pad Dimensions



Note: We recommend there is no circuit design between pads to avoid circuit short


REVISION : A0

PAGE : 6 OF 7

7. Packaging

7-1 Dimensions

7-1-1 Tape packaging dimensions




* Pre-emptied holes: 150 holes (or 30cm) or more.

| Code letter | A | В |
|-------------|-----------------|-----------------|
| Dimension | 1.45 ± 0.10 | 2.25 ± 0.10 |

Unit: mm

7-1-2 Reel Dimensions (Plastic reel : Correspond with EIAJ RRV08B)




REVISION : A0

PAGE : 7 OF 7

7-2 Peel force of top cover tape

The peel speed shall be about 300 mm / min.

The peel force of top cover tape shall be between 0.1 to 0.7 N.



7-3 Numbers of taping

5,000 pieces / reel

7-4 Making

The following items shall be marked on the reel.

- (1) Type designation
- (2) Quantity
- (3) Manufacturing date code
- (4) Manufacturer's name
- (5) The country of origin