REVISION : A1

PAGE : 1 OF 7

SPECIFICATION FOR APPROVAL


1/3W, 0805 Low Resistance Chip Resistor (Lead / Halogen free)

1. Scope

This specification applies to 1.2mm x 2.0mm size 1/3W, fixe metal film chip resistors rectangular type for use in electronic equipment.

(4)

2. Type Designation



3. Construction and Physical Dimensions




Figure 1. Structure (No mark)

Code Letter	Dimensions (mm)	
L	1.3 ± 0.20	
W	2.0 ± 0.20	
t	0.50 ± 0.20	
a	0.35 ± 0.15	
b	0.35 ± 0.15	

NOTE:

- Resistive element (under protection film)
- ② Electrode
- 3 Protection film
- 4 Substrate

REVISION : A1
PAGE : 2 OF 7

4. Ratings

4-1 Specification

Power Rating*	1/3 W	
Resistance Range	0.005Ω ~ 0.030Ω	
Resistance Tolerance	±1%, ±2%, ±5%	
Temperature Coefficient of Resistance	0~200ppm/°C	

Note*:

Power Rating is based on continuous full load operation at rated ambient temperature of 70° C. For resistors operated at ambient temperature in excess of 70° C, the maximum load shall be derated in accordance with the following curve.




Figure 2 Derating Curve

4-2 Rated Voltage

The rated voltage shall be determined by the following expression.

$$V = \sqrt{P \times R}$$
 Where V: Rated voltage (V)

R: Nominal resistance value (Ω)

P: Rated dissipation (W)

4-3 Operating and Storage Temperature Range



REVISION : A1
PAGE : 3 OF 7

SPECIFICATION FOR APPROVAL

Test Item	Condition of Test	Requirements
Short Time Overload	5 * Rated power for 5 seconds Refer to JIS C 5201-1 4.13	$\Delta R: \pm (0.5\% + 0.0005\Omega)$ Without significant damage by flashover (spark, arching), burning or breakdown etc.
Insulation Resistance	The resistor shall be cramped in the metal block and tested , as shown below. Test voltage : $100 \pm 15 V_{DC}$ for 1 minute Refer to JIS C 5201-1 4.6 Mounting condition G.	Between Electrode and Protection Film $100M\Omega$ or over Between Electrode and Substrate $1{,}000M\Omega$ or over
Voltage Proof	The voltage : 100V _{AC} (rms.) for 1 minute Refer to JIS C 5201-1 4.7	$\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without damage by flashover, fire or breakdown, as shown below.
Thermal Shock	-55 ~125°C 5 cycles, 15 min at each extreme condition Refer to JIS C 5201-1 4.19	$\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance
Low Temperature Storage	Kept at -55°C, 1,000 hours Refer to JIS C 5201-1 4.23.4	$\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance
High Temperature Exposure	Kept at 125°C for 1,000 hours Refer to JIS C 5201-1 4.23.2	$\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance
Solderability	Temperature of Solder : $245 \pm 5^{\circ}$ C Immersion Duration : 2 ± 0.5 second Refer to JIS C 5201-1 4.17	Uniform coating of solder cover minimum of 95% surface being immersed
Resistance to Soldering Heat	Dipped into solder at $270 \pm 5^{\circ}$ C for 10 ± 1 seconds Refer to JIS C 5201-1 4.18	$\Delta R: \pm (0.5\% + 0.0005\Omega)$ Without distinct deformation in appearance

REVISION : A1


PAGE : 4 OF 7

Test Item	Condition of Test	Requirements
Load Life	Rated voltage for 1.5 hours followed by a pause 0.5 hour at $70 \pm 2^{\circ}$ C. Cycle repeated 1000 hours Refer to JIS C 5201-1 4.25	$\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance
Damp Heat with Load	40 ± 2°C with relative humidity 90% to 95%. D.C. rated voltage for 1.5 hours ON and 30 minutes OFF. Cycle repeated 1,000 hours Refer to JIS C 5201-1 4.24	$\Delta R: \pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance
Mechanical Shock	100 G's for 6milliseconds. 5 pulses Refer to JIS C 5201-1 4.21	$ \Delta R: \pm (0.5\% + 0.0005\Omega) $ Without mechanical damage such as break
Bending Test	Glass-Epoxy board thickness: 1.6mm Bending width: 2mm Between the fulcrums: 90mm Refer to JIS C 5201-1 4.33	$\begin{array}{l} \Delta R: \pm (1.0\% + 0.0005\Omega) \\ Without mechanical damage such \\ as break \end{array}$

REVISION : A1

PAGE : 5 OF 7

6. Recommended Solder Pad Dimensions



Note: We recommend there is no circuit design between pads to avoid circuit short

REVISION : A1

Unit: mm


PAGE : 6 OF 7

SPECIFICATION FOR APPROVAL

7. Packaging

7-1 Dimensions


7-1-1 Tape packaging dimensions



* Pre-emptied holes: 150 holes (or 30cm) or more.

Code letter	A	В
Dimension	1.45 ± 0.10	2.25 ± 0.10

7-1-2 Reel Dimensions (Plastic reel : Correspond with EIAJ RRV08B)




REVISION : A1

PAGE: 7 OF 7

7-2 Peel force of top cover tape

The peel speed shall be about 300 mm / min.

The peel force of top cover tape shall be between 0.1 to 0.7 N.



7-3 Numbers of taping

5,000 pieces / reel

7-4 Making

The following items shall be marked on the reel.

- (1) Type designation
- (2) Quantity
- (3) Manufacturing date code
- (4) Manufacturer's name
- (5) The country of origin