



## EV CHARGING SOLUTION

### DC Charger / DC Wallbox 25kW

#### Features

- CCS / CHAdeMO dual charging ports
- Max. 94% power efficiency
- RFID card reader for user authentication
- Network connectivity (OCPP 1.5S and 1.6J)
- IP55 protection and IK08 vandal-proof casing



Highway  
Service



Parking  
Lot



Service  
Station



Commercial  
Building



Fleet



# DELTA

# Compact Design for EV Charging Services

Delta's dual output DC Wallbox advances EV compatibility at public charging sites. Its wall-mounted and modular design ensures cost-efficient installation and lifecycle maintenance. It also features built-in network connectivity for authentication and remote control applications.



## Specifications

Part Number	EVDE25-
<b>Power Input</b>	
Input Rating	380-415 Vac; 50 / 60 Hz; Three-phase / L1, L2, L3, N, PE; 50A max 230 Vac; 50 / 60 Hz; Three-phase / L1, L2, L3, PE; 90A max
Grid Type	Support TN, TT and IT power grid.
Power Factor	> 0.98
Current THD	Compliant with IEC 61000-3-12
Efficiency	94% at nominal output power
Stand-by Consumption	< 20 W
<b>Power Output</b>	
DC Output #1	IEC CCS DC Level 2, 50-500 Vdc, 60A max., 25kW max.
DC Output #2	CHAdeMO, 50-500 Vdc, 60A max., 25 kW max.
<b>Protection</b>	
Protection	Over current, Under voltage, Over voltage, Surge protection, Short circuit, Over temperature, Ground fault
<b>User Interface &amp; Control</b>	
Display	2.7" OLED screen
Support Language	English, French, German, Spanish (other languages available upon request)
Push Buttons	Multi-functional buttons (LED light: Orange, Blue) / Emergency stop button (Red)
User Authentication	ISO/IEC 14443 Type A/B RFID
<b>Communication</b>	
Connectivity	OCPP 1.5S, 1.6J
Network Interface	Ethernet, Cellular
<b>Environment</b>	
Operating Temperature	-30°C to +50°C (-22°F to +122°F) Derating from +50°C to +60°C (+122°F to +140°F)
Storage Temperature	-40°C to +85°C (-40°F to +185°F)
Humidity	< 95% relative humidity, non-condensing
Altitude	Up to 2,000 m (6,500 ft.)
<b>Mechanical Design</b>	
Ingress Protection	IP55
Enclosure Protection	IK08
Cooling	Forced air
Charging Cable Length	4 m (13 ft.) (standard) / 7 m (23 ft.) (optional for IEC CCS DC)
Dimension (W x H x D) / Weight	680 x 430 x 230 mm (27 x 17 x 9 inch) / 43 kg (95 lb), excluding plug and cable
Mounting	Wall-mount or optional stand
<b>Regulation</b>	
Certificate	CE
Compliance	CHAdeMO / IEC 61851-1 / IEC 61851-23

Note1 : Single output model is available.

Note2 : Specifications are subject to change without notice.

## Delta Electronics Europe

Zandsteen 15, 2132 MZ Hoofddorp, The Netherlands

TEL : +31 20 655 0900 / FAX : +31 20 655 0999

E-mail : [evcs@deltaww.com](mailto:evcs@deltaww.com)

[www.deltaww.com/evcs](http://www.deltaww.com/evcs)

