# ESOA300-HAF Hybrid Series

### **Outdoor Power System**



To ensure the whole site functions superbly, besides the gorgeous power system, the tailor-made enclosure is essential. No doubt, ESOA300-HAF Hybrid Series is the elegant choice in Outdoor Power System.

ESOA300-HAF Hybrid Series offers several enclosure sizes, for the space-critical condition, this is one of the important factors to achieve the goal of space usage efficiency.

The whole system combines high power density rectifiers, intelligent controller and adaptable PDUs, performing in high level in a robust enclosure.

Besides well protected by IP55 class enclosure, highly flexible thermal system can overcome different environmental challenges, that is, not only the battery life can be lengthened, but the sensitive system can work in a perfect condition.

#### **Key Features**

- -48V DC output for telecommunication applications
- IP55 protection class for outdoor application
- Compact dimension in height to reduce cabinet size
- Perfectly integrated with Delta
   Telecom Power system controller
- Day and night acoustic noise internal / external fan speed control

#### **Applications**

- 3G / 4G / 5G
- Fixed Line
- Datacom



## ESOA300-HAF Hybrid Series



INPUT GOCACS-03-ZL

	000/00-00-22
Voltage (nominal)	Single phase; $220V_{AC}$ ; $3W$ (L, N, PE) Three phase; $V_{L-L}$ : $380V_{AC}$ ; $V_{L-N}$ : $220V_{AC}$ ; $5W$ (L1, L2, L3, N, PE)
Voltage (range)	Single phase; 90 - $300V_{AC}$ ; De-rating $\leq 176V_{AC}$ Three phase; $V_{L-L}$ : $380/400/415$ ( $\pm 20\%$ ); $V_{L-N}$ : $220/230/240$ ( $\pm 20\%$ )
Frequency	45 - 66Hz
OUTPUT	
Voltage (nominal)	-54V <sub>DC</sub>
Voltage (default)	-54V <sub>DC</sub>
Voltage (adjustable range)	-43 to -58V <sub>DC</sub>
Maximum Power @ nominal Input	17.4kW from rectifier; 13.2kW from PV charger
MECHANICAL	
Dimensions (W x H x D)	800 x 2060 x 750mm (31.49 x 81.10 x 29.52in)
Weight	approx. 170kg (374.78lb) (without rectifier, external, cooling unit)
IP Protection	IP 55
ENVIRONMENTAL	
Operating Temperature	0 to +50 °C (32 to +122 °F)
Storage Temperature	-40 to +70 °C (-40 to +158 °F)
Altitude	0 to +3000m
Related Humidity	95%, non-condensing (Max.)
Acoustic Noise	≤ 65dBA
Cooling Capacity	Fan: 250W/K
STANDARDS	
Safety	IEC/EN60950
EMC	EN 300 386 Conduction: class A Radiation: class B
Environment	RoHS
<u> </u>	

#### Delta Electronics Inc.

3 Tungyuan Road, Chungli Industrial Zone, Taoyuan City 32063, Taiwan.

T +886 3 452 6107 / F +886 3 452 7314

www.deltaww.com

 $\ensuremath{^\star}$  All specifications are subject to change without prior notice.

