

ENERGY STORAGE SOLUTION

Power Conditioning System / PCS100

Features

- Power capacity: 100 kW; AC voltage: 400 Vac
- High efficiency: Peak 97.9%
- High power density:118W/I, 323 W/kg
- Quick power transfer time (<40 ms)
- IP55 for outdoor application
- Black start capability for power backup and microgrid applications
- Scalable with multiple units in configuration














The Leading Power for Energy Storage

Delta Power Conditioning System (PCS) is a bi-directional energy storage inverter for grid-tied and off-grid applications including power backup, peak shaving, load shifting, PV self-consumption, PV smoothing and etc. It demonstrates industry leading power performance with high power efficiency and low stand-by power loss. It is compact for space saving and offers scalability for various system configurations and integration with mainstream branded battery systems.



System Architecture



Applications

- Real and reactive power compensation to improve power quality
- Standalone operation for power backup
- Demand charge management / peak shaving
- · Load shifting for time-of-use savings

Specifications

Model Name	PCS100
AC Connection	
Rated Grid Voltage	400 Vac, 3P3W
Grid Voltage Range	320 ~ 440 Vac (VDE-AR-N4105) 1) 312 ~ 450 Vac (AS/NZS 4777.2) 2) 320 ~ 456 Vac (G99) 1)
Rated Grid Frequency	50 (60 Hz optional)
Frequency Range	47.5 ~ 51.5 Hz (VDE-AR-N4105) 47 ~ 52 Hz (AS/NZS 4777.2, AS) 47.5 ~ 52 Hz (G99) 45 ~ 52 Hz (AS/NZS 4777.2, NZS)
Rated AC Power / Current	100 kVA / 144.3 A
Max. Continuous AC Current	160.4 Arms
Current THD	< 3%
Power Factor	-1 to 1, continuously adjustable
DC Connection	
DC Voltage Range	600 ~ 1,000 Vdc
Rated DC Voltage	900 Vdc
Rated Discharge / Charge Power	103 kW / 97 kW
Max. Discharge / Charge Current	171.7 A/161.7 A for CE mark 137.3 A/129.3 A for RCM mark
Standalone Operation	
Rated Output Voltage	400 Vac, 3P3W
Rated Output Power	100 kVA / 100 kW with linear load; 100 kVA with RCD load (CF≤2)³)
Rated Output Current	144.3 A
Power Factor	0.8 ~ 1
Output Voltage THD	< 3% @ linear load < 5% @ RCD load (CF≤2)
Performance	
Peak Efficiency	97.9%
Standby Loss	< 25W @ sleep mode
Environment	
Max. Altitude	3,000 m, de-rating above 2,000 m
Operating Temperature	-25 °C to +60 °C, de-rating @ > 50°C
Humidity	0 to 95% RH, non-condensing
Acoustic Noise	< 72 dBA @ 1 m @ rated condition
Cooling	Forced air with speed control
Enclosure Rating	IP55
General	
User Interface	4.9" LCD screen
Emergency Stop	EPO button & remote control
Communication	RS-485 / Modbus RTU, CAN
Dimension (W x H x D)	600 x 1766 x 800 mm
Net Weight	310 kg
Certificate	Safety: IEC/EN 62477-1, AS 62040.1.1 Grid Code: VDE-AR-N4105, G99, AS/NZS 4777.2 EMC: IEC/EN 61000-6-2, IEC/EN 61000-6-4 (Class A)
Product Conformity	CE, RCM
Applicable Battery Chemistry	Lithium-ion, lead-acid, flow battery



^{1) @}DC Voltage Range: 700 ~ 1000 V 2) @DC Voltage Range: 750 ~ 1000 V 3) Transformer or motor load, which has large inrush current (CF>2) is not included * Specifications are subject to change without prior notice



Delta Electronics Europe

Zandsteen 15, 2132 MZ Hoofddorp, The Netherlands

TEL: +31 20 655-0900 FAX: +31 20 655-0999 PCS@deltaww.com

Delta Electronics Australia

20-21/45 Normanby Road Notting Hill, VIC 3168, Australia

TEL: +61-3-9543-3720 FAX: +61-3-9544-0606 PCS@deltaww.com

www.deltaww.com 2020 / 06