








Picture	Part number	Dimension (mm)	Operating Voltage Range (VDC)	Voltage (VDC)	Current (A)	Power (W)	Speed (RPM)	Noise (dB-A)	Air Flow	Air Pressure
	ASB0612MB-00	66x66x15	6.0 ~ 13.8	12.0	0.06	0.72	3600	28.0	17.000 CFM 0.483 M ³ /min	0.098 inchH ₂ O 2.550 mmH ₂ O
	AUB0812LJ-00	80x80x25	7.0 ~ 13.8	12.0	0.03	0.36	1800	16.0	21.000 CFM 0.594 M ³ /min	0.056 inchH ₂ O 1.430 mmH ₂ O
	AUB0912LJ-03	92x92x25	7.0 ~ 13.8	12.0	0.05	0.60	1840	20.5	26.100 CFM 0.739 M ³ /min	0.066 inchH ₂ O 1.688 mmH ₂ O
	EUB0912HF-03	92x92x32	10.8 ~ 13.2	12.0	0.12	1.44	3350	33.5	47.002 CFM 1.330 M ³ /min	0.227 inchH ₂ O 5.760 mmH ₂ O
	EUB0912LF-03		10.8 ~ 13.2	12.0	0.05	0.60	2550	27.5	34.987 CFM 0.990 M ³ /min	0.128 inchH ₂ O 3.260 mmH ₂ O
	EUB1212MJ-00	113x113x45	7.0 ~ 13.2	12.0	0.11	1.32	2650	31.0	52.800 CFM 1.494 M ³ /min	0.161 inchH ₂ O 4.090 mmH ₂ O
	EUB1312HE-10	125x125x52	10.8 ~ 13.2	12.0	0.13	1.56	2200	32.0	79.868 CFM 2.260 M ³ /min	0.183 inchH ₂ O 4.660 mmH ₂ O
	EUB1312ME-10		10.8 ~ 13.2	12.0	0.08	0.96	1800	26.0	62.198 CFM 1.760 M ³ /min	0.128 inchH ₂ O 3.240 mmH ₂ O
	KSB1212ME-03	Φ120.0x43.0	10.8 ~ 13.2	12.0	0.19	2.28	1800	36.2	44.952 CFM 1.272 M ³ /min	0.300 inchH ₂ O 7.620 mmH ₂ O
	KSB1212LE-03		10.8 ~ 13.2	12.0	0.11	1.32	1450	30.0	33.573 CFM 0.950 M ³ /min	0.177 inchH ₂ O 4.500 mmH ₂ O