

Modbus TCP/IP (6 Digits)

HMI Factory Setting:

Controller IP Address: 192.168.0.1

Controller COM Port: 502

Controller Station Number: 1

Control Area / Status Area: W4-1 / W4-11

Connection

Standard Jumper Cable / Network Cable without jumper (Auto-detected by HMI)

Definition of PLC Read/Write Address

a. Registers

Type	Format	Read/Write Range	Data Length	Note
	Word No. (n)			
Output Registers	W4-n	W4-00001 - W4-65535	Word	
Input Registers	W3-n	W3-00001 - W3-65535	Word	Read only

b. Contacts

Type	Format	Read/Write Range	Note
	Bit No. (b)		
Discrete Outputs	B0-b	B0-00001 - B0-65535	
Discrete Inputs	B1-b	B0-00001 - B0-65535	Read only

- 1.) This communication protocol supports 2 special parameter. If the controller requests certain Modbus input during the connection, it can be done through set special parameter 1 which default value is set to Auto that will automatically react to a single inputted command(0x06) or a multiple inputted command (0x10) according to the data length; and special parameter 2 can set order of data which default value is Low word first.

