

## Mitsubishi A Series (CPU Port)

(Supporting A2A, A2AS, A2USH, A1SH, A3N, A2ASH(CPU-S1) Series)

### HMI Factory Setting:

Baud rate: 9600, 8, ODD, 1

Controller Station Number: 0 (no PLC station number in protocol, therefore, only 1(HMI) to 1(PLC) communication is allowed.)

Control Area / Status Area: D0/D10

### Connection

#### a. RS-422 (DOP-A/AE Series)

| DOP Series                |       | Controller                |  |
|---------------------------|-------|---------------------------|--|
| 9 pin D-SUB male (RS-422) |       | 25 pin D-SUB male(RS-422) |  |
| RXD+ (2)                  | ————— | (3) SDB (TXD+)            |  |
| RXD- (1)                  | ————— | (16) SDA (TXD-)           |  |
| TXD- (4)                  | ————— | (15) RDA (RXD-)           |  |
| TXD+ (3)                  | ————— | (2) RDB (RXD+)            |  |
| RTS+ (7)                  | ————— | (4) CTS+                  |  |
| CTS+ (8)                  | ————— | (5) RTS+                  |  |
| RTS- (6)                  | ————— | (17) CTS-                 |  |
| CTS- (9)                  | ————— | (18) RTS-                 |  |

**b. RS-422 (DOP-AS57 Series)**

| DOP Series                |       | Controller                |  |
|---------------------------|-------|---------------------------|--|
| 9 pin D-SUB male (RS-422) |       | 25 pin D-SUB male(RS-422) |  |
| R+(COM2)                  | ————— | (3) SDB (TXD+)            |  |
| R-(COM2)                  | ————— | (16) SDA (TXD-)           |  |
| T-(COM2)                  | ————— | (15) RDA (RXD-)           |  |
| T+(COM2)                  | ————— | (2) RDB (RXD+)            |  |
| T+(COM3)                  | ————— | (4) CTS+                  |  |
| R+(COM3)                  | ————— | (5) RTS+                  |  |
| T-(COM3)                  | ————— | (17) CTS-                 |  |
| R-(COM3)                  | ————— | (18) RTS-                 |  |

**c. RS-422 (DOP-B Series)**

| DOP Series                | Controller                |
|---------------------------|---------------------------|
| 9 pin D-SUB male (RS-422) | 25 pin D-SUB male(RS-422) |
| RXD+ (COM2-4)             | (3) SDB (TXD+)            |
| RXD- (COM2-9)             | (16) SDA (TXD-)           |
| TXD- (COM2-6)             | (15) RDA (RXD-)           |
| TXD+ (COM2-1)             | (2) RDB (RXD+)            |
| RTS+ (COM3-1)             | (4) CTS+                  |
| CTS+ (COM3-4)             | (5) RTS+                  |
| RTS- (COM3-6)             | (17) CTS-                 |
| CTS- (COM3-9)             | (18) RTS-                 |

**Definition of PLC Read/Write Address**

**a. Registers**

| Type                   | Format       | Read/Write Range | Data Length | Note   |
|------------------------|--------------|------------------|-------------|--|
|                        | Word No. (n) |                  |             |  |
| Input                  | Xn           | X0 - X7FF        | Word        | Hexadecimal, <a href="#">1</a> , <a href="#">4</a> |
| Output                 | Yn           | Y0 - Y7FF        | Word        | Hexadecimal, <a href="#">1</a>                     |
| Link Relay             | Bn           | B0 - BFFF        | Word        | Hexadecimal, <a href="#">1</a>                     |
| Internal Relay         | Mn           | M0 - M8191       | Word        | <a href="#">1</a>                                  |
| Special Internal Relay | SMn          | SM9000 - SM9255  | Word        | <a href="#">2</a>                                  |
| Latch Relay            | Ln           | L0 - L8191       | Word        | <a href="#">1</a>                                  |

| Type                  | Format          | Read/Write Range | Data Length | Note  |
|-----------------------|-----------------|------------------|-------------|---|
|                       | Word No. (n)    |                  |             |   |
| Annunciator           | F <sub>n</sub>  | F0 - F2047       | Word        | <a href="#">1</a>                                     |
| Timer Value           | TN <sub>n</sub> | TN0 - TN2047     | Word        |   |
| Counter Value         | CN <sub>n</sub> | CN0 - CN1023     | Word        |   |
| Data Register         | D <sub>n</sub>  | D0 - D8191       | Word        |   |
| Special Data Register | SD <sub>n</sub> | SD9000 - SD9255  | Word        |   |
| File Register         | R <sub>n</sub>  | R0 - R8191       | Word        |   |
| Link Register         | W <sub>n</sub>  | W0 - WFFF        | Word        | Hexadecimal   |
| Input Card Register   | PX <sub>n</sub> | PX0 - PX7FF      | Word        | Hexadecimal,<br><a href="#">1</a> , <a href="#">4</a> |

**b. Contacts**

| Type                   | Format          | Read/Write Range | Note                              |
|------------------------|-----------------|------------------|-----------------------------------|
|                        | Bit No. (b)     |                  |                                   |
| Input                  | X <sub>b</sub>  | X0 - X7FF        | Hexadecimal,<br><a href="#">4</a> |
| Output                 | Y <sub>b</sub>  | Y0 - Y7FF        | Hexadecimal                       |
| Link Relay             | B <sub>b</sub>  | B0 - BFFF        | Hexadecimal                       |
| Internal Relay         | M <sub>b</sub>  | M0 - M8191       |                                   |
| Special Internal Relay | SM <sub>b</sub> | SM9000 - SM9255  |                                   |
| Latch Relay            | L <sub>b</sub>  | L0 - L2047       |                                   |
| Annunciator            | F <sub>b</sub>  | F0 - F2047       |                                   |
| Timer Contact          | TS <sub>b</sub> | TS0 - TS2047     |                                   |
| Timer Coil             | TC <sub>b</sub> | TC0 - TC2047     |                                   |
| Counter Contact        | CS <sub>b</sub> | CS0 - CS1023     |                                   |
| Counter Coil           | CC <sub>b</sub> | CC0 - CC1023     |                                   |
| Input Card Register    | PX <sub>b</sub> | PX0 - PX7FF      | Hexadecimal,<br><a href="#">4</a> |

 **NOTE**

- 1) Device address must be the multiple of 16.
- 2) Device address must be 9000 plus the multiple of 16.
- 3) If the PLC station number is set as 0 and a read/write register error occurs on HMI, please reset the PLC station number to 255.
- 4) If a read/ write register X error occurs on HMI, please use register PX.

- 5) R address would vary upon the FILE REGISTER of PLC setting.

For Example : A2USH

1K : 3800-4000H

2K : 3000-4000H

3K : 2800-4000H

4K : 2000-4000H

5K~8K : ...

FILE REGISTER : PLC must be on or Read/Write will be incorrect..

- 6) How to set File Register (R) for Mitsubishi A serial PLC:

1. Startup MELSOFT series GX Developer.
2. Open "Project Data List" windows. ("View" Option)
3. Double click Parameter \ PLC Parameter, and open "Setting" window.
4. Set Memory Capacity \ File Register (0 ~8).
5. Press "End" button on the bottom and complete the setting.
6. Execute OnLine\Write to PLC.
7. Enable the "Parameter \ PLC/Network" and "File register \ Main" option (check the check box next to "Parameter \ PLC/Network" and "File register \ Main").
8. Press "Execute" button.
9. Complete