

Modbus nW RTU / ASCII (Master)

HMI Factory Setting:

Baud rate: 9600, 7, Even, 1.(ASCII); 9600, 8, Even, 1.(RTU)

Controller Station Number: 1 ([Note1](#))

Control Area / Status Area: W40100 / W40200

Connection

Please refer to “Pin Definition of Serial Communication” for more detail.

Definition of PLC Read/Write Address

a. Registers

Type	Format	Read/Write Range	Data Length	Note
	Word No. (n)			
Output Registers	Wn	W40001 - W50000	Word	
Input Registers	Wn	W30001 - W40000	Word	

b. Contacts

Type	Format	Read/Write Range	Note
	Bit No. (b)		
Discrete Outputs	Bb	B1 - B10000	
Discrete Inputs	Bb	B10001 - B20000	

NOTE

- 1) This communication protocol does not support station 0 (the broadcast function).
- 2) To attain optimize reading, please ensure the “Optimize” option is selected in communication setting. Do not select “Data Length Limit” if “Optimize” option is not selected,
- 3) 984RTU(Master) is Modbus standard communication programming; RTU nW(master) is special communication programming, they are same except following three divergence.
 - a. Broadcast
 - i. 984RTU(Master), Controller Station Number 0 is broadcast.

- ii. RTU nW(Master) is no broadcast, Controller Station Number 0 is normal station.
- b. Register Input
 - i. 984RTU(Master) has two inputted command, single inputted command(0x06) or a multiple inputted command (0x10).
 - ii. RTU nW(Master) only has one inputted command(0x10).
- c. Contacts output
 - i. 984RTU(Master) only got one contact for once communication.
 - ii. RTU nW(Master) only got 16 contacts for once communication. · it is special specification.