

Siemens S7 300 (with PC adapter)

HMI Factory Setting:


Baud rate: 19200, 8, Even, 1

Controller Station Number: 2([Note1](#), [Note2](#), [Note3](#))

Control Area / Status Area: DBW0/DBW20

Connection

a. RS-232 (via PC adapter) (DOP-A/AE/AS, DOP-B Series)



Definition of PLC Read/Write Address

a. Registers

Type	Format	Read/Write Range	Data Length	Note
	Word No.(n) Bank No.(m)			
Input Image	IWn	IW0 - IW65534	Word	
	IDn	ID0 - ID65532	Double Word	
Output Image	QWn	QW0 - QW65534	Word	
	QDn	QD0 - QD65532	Double Word	
Internal Bits	MWn	MW0 - MW65534	Word	
	MDn	MD0 - MD65532	Double Word	
Data Area	DBm.DBWn	DB1.DBW0 - DB255.DBW65534	Word	4

b. Contacts

Type	Format	Read/Write Range	Note
	Word No.(n) Bank No.(m) Bit No.(b)		
Input Image	In.b	I0.0 – I65535.7	
Output Image	Qn.b	Q0.0 – Q65535.7	
Internal Bits	Mn.b	M0.0 – M65535.7	
Data Area	DBm.DBXn.b	DB1.DBX0.0 – DB255.DBX65535.7	4
Data Area (DB10)	DBXn.b	DBX0.0 – DBX65535.7	
	Vn.b	V0.0 – V65535.7	

 **NOTE**

- 1) Communication via PC adapter, PLC station will not be used, therefore, only 1(HMI) to 1 (PLC) communication is allowed.
- 2) Baud rate setting of PLC must be 187.5kps or above (but not 19.2kps). For HMI, the baud rate can only be 19.2kbps or 28.4kbps (by the Switch setting of PC adapter).
- 3) Set up both ends of PC adapter for PLC connection and HMI connection (one end to one connection). Once PLC is connected, the Power LED signal will be on instantly and the LED signal would blink only during the communication. If communication failure occurs, the LED signal will remain off.
- 4) PLC needs to enable DB memory (DBm.DBWn、DBm.DBDn、DBm.DBXn.b) before DB data can be read.
- 5) Timer reads only up to 3 digits. If a value input is more than 3 digits, the Timer will regards the highest 3 (decimal) and replace the rest by 0. For example, a value 12345 will be written as 12300 in PLC.
- 6) Counter reads only up to 3 digits. If a value input is more than 3 digits, the Counter will regards the first 3 digits and leave out the rest. For example, a value 12345 will be written as 123 in PLC.
- 7) Except register Tn and Cn , data type of register is Byte and its order is opposite to usual controller , for example :
 - 1、IW3 is a word which combined from IB3 and IB4 , High Byte of IW3 is IB3 ; Low Byte of IW3 is IB4.

- 2、 ID3 is Double Word which combined from IB3, IB4, IB5 and IB6, and its order from highest to lowest is IB3, IB4, IB5 and IB6.

And please be attentive to use these registers, because their Data type is different with Data Length, it will need more than one register for each access, for example:

- 1、 AIW6 which Data Type is Byte and Data Length is 1 Word, when it used for one word Numeric Entry , it will occupy two addresses AIB6 and AIB7 .
- 2、 MD12 which Data Type is Byte and Data Length is Double Word , when it used for one word Numeric Entry, it will occupy four addresses MB12,MB13,MB14 and MB15; But data only stored in MB14 and MB15.
- 3、 IW3 which Data Type is Byte and Data Length is 1 Word , when it used for double word Numeric Entry, it will occupy for addresses IB3,IB4,IB5 and IB6 , order from highest to lowest byte is IB5,IB6,IB3 和 IB4.