



## Multi - Vehicle Ultra - Fast Charging Solution

# DC Charger / UFC 200

- 200 kW charging power for next generation e-vehicles
- Dynamic power management minimizing the charging time
- Integrated credit card payment solution and RFID user identification
- Connector on both sides for different traffic schemes



Fast Charging  
Corridors



Parking



Service  
Station



Traffic  
Hub



Logistics  
Fleet



# Forward-Looking EV Infrastructure

## Speed-up your power with UFC 200


Delta's UFC 200 platform offers the convenience of a single charging station with the flexibility to charge up to four vehicles simultaneously. Two charging points are available for DC fast charging up to 200 kW and two charging points for AC charging with 22 kW each. Thanks to the integrated power management, the available power can be optimised, the charging times of

the vehicles can be reduced and the maximum currents at the grid connection point can be secured at all times. For larger DC charging parks, additional variants and configurations are possible to optimize operation or to implement different traffic and parking concepts.



## Application Scenario

### Charging Network




### Backend System

DeltaGrid® EV Management System



### Applications



... and more

## Feature Highlights



### Efficient Charging Service

- Simultaneous Charging up to four vehicles
- Dynamic Load Distribution
- 94% Power Efficiency
- 400A CCS cable without liquid cooling
- Supports up to 920 VDC



### Complete System Integration

- Network Connectivity
- Backend Compatibility
- Energy Management
- Interoperability with EV



### Optimal Operation

- All-Weather Outdoor Design
- Low Lifecycle Cost
- High Availability Service
- German Eichrecht Conformity



## Product at a Glance

### Network Connectivity

Ethernet, Cellular 2G / 3G / 4G

### User Authentication

Credit card, RFID reader, Autocharge  
Prepared for ISO 15118-2

### Protection

IP55, IK10



### Accessibility

According to DIN 18040

### Charging Standard

- CCS up to 200 kW / 400A
- CHAdeMO up to 62.5 kW
- AC Type 2 charging ports 2× 22 kW
- Choice of plug standard

# Specifications

Model Name		UFC 200
<b>Input</b>		
AC Connection	3-Phase, L1, L2, L3, N, PE	
AC Voltage	400 V <sub>RMS</sub> (L-L) ± 10 %	
Frequency	50 / 60 Hz	
Nominal Current	380 A <sub>RMS</sub> at maximum power (200 kW DC + 44 kW AC)	
Power Factor / THDu	0.99 / 1.5 %	
Mains Terminal	Terminal blocks	
Transient OVP	Class II / C protection	
<b>Output</b>		
DC Output Voltage Range	200 V to 920 V <sub>DC</sub>	
Maximum Current	500 A <sub>DC</sub> at 400 V <sub>DC</sub> / 250 A <sub>DC</sub> at 800 V <sub>DC</sub>	
Maximum Power	200 kW <sub>DC</sub>	
Cable Length / Reach Distance	3.2 m / 2.2 m (option 5 m / 3.7 m)	
Protection	Over current, Under voltage, Over voltage, Short circuit, Ground fault and Isolation monitoring	
<b>User Interface &amp; Control</b>		
Display	7 inch LCD	
Supported Languages	English (Up to 4 additional languages available on request)	
Push Button	1 Emergency Stop Button (option)	
Keypad	5 buttons	
Local Authentication	RFID and NFC Credit card terminal option, Autocharge	
Network Interface	Ethernet, Cellular, 2 G / 3 G / 4 G	
Protocol	Back-end system integration with OCPP 1.5 and 1.6 (HW readiness for OCPP 2.0) Modbus TCP for load management / energy management system integration	
<b>Environmental</b>		
Operating Temperature	-25 °C to +50 °C	
Storage Temperature	-40 °C to +80 °C	
Humidity	< 95% relative humidity, non-condensing	
Altitude	Up to 2000 m	
<b>Mechanical</b>		
Ingress Protection	IP55	
Enclosure Protection	IK10 on the enclosure, IK08 on the display (according to IEC 62262)	
Cooling	Forced air	
Dimension (W x H x D)	2079 × 859 × 998 mm	
Weight *	550 kg*	
<b>Regulation</b>		
Safety	IEC 61851-1, IEC 61851-23, IEC 62479-1/-7	
EMC	EN 55011, IEC 61851-21-2	
German Eichrecht	Fully Compliant	
Accessibility	DIN 18040	
<b>DC Charging Points</b>		<b>CHAdemo</b>
Rating cable and connector	400 A <sub>DC</sub>	125 A <sub>DC</sub> / 500 V <sub>DC</sub>
Compliance	IEC 61851-23 / -24, IEC 62196-3, DIN 70121 Prepared for ISO 15118-2	IEC 61851-23 / -24, JEVS G 105, Rev. 1.2 compliant
<b>AC Charging Point</b>		
Nominal AC Voltage	400 V <sub>RMS</sub>	
Type 2 AC Plug / Connector	3 × 32 A <sub>RMS</sub> at 22 kW	
Protections	RCD Type A 30 mA+ 6 mA DC leakage current detection, compliant to IEC 62955	
Compliance AC connector & socket	IEC 62196-2 Mode 3, Type 2	

\* Dimension and weight including charging connectors, subject to variants.

Product outlook depends on configuration. Specifications are subject to change without notice.



More information

## Delta Electronics (Netherlands) BV

Zandsteen 15, 2132 MZ Hoofddorp, The Netherlands

TEL : +31 20 655-0900

[www.delta-emea.com](http://www.delta-emea.com)



2023/10