



# RGB Slim Laser Video Wall


## 70" Full HD RGB Laser Slim Video Wall

- Rich picture quality with Full HD Resolution for superb image quality
- Ultra High Brightness to give the most vivid colors
- High lumens efficiency for reducing operating costs
- Browser/Server based architecture for quick monitoring
- Slimmest Laser Cube saves real state
- 



# 70" Full HD RGB Laser Slim Video Wall

Delta's Laser Video wall is a rear projection, Laser based Full HD Video wall that offers environment friendly Laser illumination, ultra high brightness and true cube redundancy. Industry's first ultra-bright Laser based DLP® video wall improves energy savings of up to 33%.



LED Light Source



RGB Laser Light Source

## Specifications

| Model  |             | DVS-708RS AM / DVS-708FS AM   |                       |                       |                                   |        |
|--|-------------|---|-----------------------|-----------------------|-----------------------------------|--------|
| Description                                      |             | RGB Laser Light Source Full HD Cube                                       |                       |                       |                                   |        |
| Individual Cube Size                             |             | 70" Diagonal  |                       |                       |                                   |        |
| Image Size                                       |             | 1550 x 872 mm   |                       |                       |                                   |        |
| Display Technology                               |             | DLP, single chip  |                       |                       |                                   |        |
| Native Resolution                                |             | 1920 x 1080 pixels  |                       |                       |                                   |        |
| Aspect Ratio                                     |             | 16:9  |                       |                       |                                   |        |
| Screen to Screen Gap                             |             | Rear Access : 0.2mm, Front Access : 1.0 mm                                |                       |                       |                                   |        |
| Light Source                                     |             | Laser (Lasers Class 1)  |                       |                       |                                   |        |
| Brightness(Bright/High Bright)                   |             | Typ. 1800 lumens <sup>*1</sup>  |                       |                       |                                   |        |
| Brightness Uniformity                            |             | Up to 95% <sup>*2</sup>   |                       |                       |                                   |        |
| Contrast Ratio                                   |             | Typ. 1800:1   |                       |                       |                                   |        |
| Colors   |             | 16.7 million  |                       |                       |                                   |        |
| Color Temperature Range                          |             | 3200K to 9300K, Custom  |                       |                       |                                   |        |
| Standard Inputs                                  |             | 1x Digital DVI-I, 2x Digital HDMI, 1x Analog D-sub 15pin, 1x Display Port |                       |                       |                                   |        |
| HDMI input support max resolution                |             | 3840x2160   |                       |                       |                                   |        |
| DP input support max resolution                  |             | 3840x2160   |                       |                       |                                   |        |
| Standard Outputs <sup>*4</sup>                   |             | 2x Digital HDMI   |                       |                       |                                   |        |
| HDMI output support max resolution               |             | 3840x2160   |                       |                       |                                   |        |
| Control Options                                  |             | RS-232 / RS 422, IP, IR   |                       |                       |                                   |        |
| Screen Brightness                                | Screen Type | Bright mode   | Normal mode           | ECO mode              | Screen Viewing Angle ( 1/2 Gain ) |        |
|  | CSI         | 520 cd/m <sup>2</sup>   | 370 cd/m <sup>2</sup> | 250 cd/m <sup>2</sup> | H: 36°                            | V: 34° |
| Light source Average Life                        |             | 60,000 hours  | 130,000 hours         | 130,000 hours         |                                   |        |
| Power Consumption <sup>*4</sup>                  |             | 200 w   | 150 w                 | 100 w                 |                                   |        |
| Heat dissipation                                 |             | 685 BTU/h   | 480 BTU/h             | 340 BTU/h             |                                   |        |
| Input Voltage                                    |             | AC 90-240 V @ 50/60 hz  |                       |                       |                                   |        |
| Noise Level (1m to Screen)                       |             | 30dB  |                       |                       |                                   |        |
| Power Supply                                     |             | Single Power supply   |                       |                       |                                   |        |
| Dimension (W x H x D) & Weight                   |             | Dimension : 1550 x 1151 x 560 mm, Net weight: Rear = 112Kg, Front = 120Kg |                       |                       |                                   |        |
| Operating Temperature                            |             | 5°C ~ 40°C (41°F ~ 104°F), Operating Altitude : <=4000m                   |                       |                       |                                   |        |
| Non-Operating Temperature ( No including Screen) |             | -20°C ~ 60°C (-4°F ~ 140°F)   |                       |                       |                                   |        |
| Non-Operating Temperature (Screen)               |             | 5°C ~ 40°C (41°F ~ 104°F)   |                       |                       |                                   |        |
| Operating / Storage Humidity                     |             | 10% ~ 90%, non-condensing   |                       |                       |                                   |        |

Note: <sup>\*1</sup>. Bright mode Engine brightness, <sup>\*2</sup>. Through electronical compensation  
<sup>\*</sup> All specifications are subject to change without prior notice. Ver:02.2023