



# Xtra Slim LED Video Wall


## 70" Full HD LED Video Wall

- Rich picture quality with Full HD Resolution for superb image quality
- Long life & environment friendly product
- High lumens efficiency for reducing operating costs
- Browser/Server based architecture for quick monitoring
- Slimmest LED Cube saves real state



# 70" Full HD LED Video Wall

Delta's LED Video wall is a rear projection, LED based Full HD Video wall that offers environment friendly LED illumination, vivid rich color and true cube redundancy. Industry's first ultra-slim LED based DLP® video wall save user's installation space .



LED Light Source



New Gen. LED Light

Source

## Specifications

| Model                          |                   | DVS-708RSL / DVS-708FSL  |   |                       |                                   |        |
|--------------------------------|-------------------|--|---|-----------------------|-----------------------------------|--------|
| Description                    |                   | LED Light Source Full HD Cube  |   |                       |                                   |        |
| Individual Cube Size           |                   | 70" Diagonal   |   |                       |                                   |        |
| Image Size                     |                   | 1550 x 872 mm  |   |                       |                                   |        |
| Display Technology             |                   | DLP, single chip   |   |                       |                                   |        |
| Native Resolution              |                   | 1920 x 1080 pixels   |   |                       |                                   |        |
| Aspect Ratio                   |                   | 16:9   |   |                       |                                   |        |
| Screen to Screen Gap           |                   | Rear Access : 0.2mm , Front Access : 1.0 mm  |   |                       |                                   |        |
| Light Source                   |                   | LED  |   |                       |                                   |        |
| Brightness Uniformity          |                   | Up to 98% <sup>*1</sup>  |   |                       |                                   |        |
| Contrast Ratio                 |                   | Typ. 1000:1  |   |                       |                                   |        |
| Colors                         |                   | 16.7 million   |   |                       |                                   |        |
| Color Temperature Range        |                   | 3200K to 9300K, Custom   |   |                       |                                   |        |
| Standard Inputs <sup>*3</sup>  |                   | 1x Digital DVI-I, 2x Digital HDMI, 1x Analog D-sub 15pin, 1x Display Port          |   |                       |                                   |        |
| Standard Outputs <sup>*3</sup> |                   | 2x Digital HDMI  |   |                       |                                   |        |
| Optional Board                 | I <sup>*2</sup>   | Inputs   | 1x Digital DVI-D, 1x HDMI, 1x Display port, 1x Analog 5BNC (RGBHV or YPbPr), 1x Analog S-video    |                       |                                   |        |
|                                | II <sup>*2</sup>  | Inputs   | 1x Digital DVI-D, 1x 3G-SDI, 1x Display port 1x Analog 5BNC (RGBHV or YPbPr), 1x Analog S-video   |                       |                                   |        |
|                                |                   | Output   | 1x 3G-SDI   |                       |                                   |        |
|                                | III <sup>*2</sup> | Inputs   | 1x Digital DVI-D, 1x HD-baseT, 1x Display port 1x Analog 5BNC (RGBHV or YPbPr), 1x Analog S-video |                       |                                   |        |
| Control Options                |                   | RS-232 / RS 422, IP, IR  |   |                       |                                   |        |
| Screen Brightness              | Screen Type       | Bright mode  | Normal mode   | ECO mode              | Screen Viewing Angle ( 1/2 Gain ) |        |
|                                | CSI               | 270 cd/m <sup>2</sup>  | 190 cd/m <sup>2</sup>   | 150 cd/m <sup>2</sup> | H: 36°                            | V: 34° |
|                                | XMD-AG            | 290 cd/m <sup>2</sup>  | 210 cd/m <sup>2</sup>   | 160 cd/m <sup>2</sup> | H: 31°                            | V: 17° |
| Light source Average Life      |                   | 60,000 hours   | 80,000 hours  | 100,000 hours         |                                   |        |
| Power Consumption              |                   | 210 w  | 180 w   | 160 w                 |                                   |        |
| Input Voltage                  |                   | AC 90-240 V @ 50/60 Hz   |   |                       |                                   |        |
| Power Supply                   |                   | Dual Power supply with Redundancy available as an option                           |   |                       |                                   |        |
| Redundancy Function            |                   | Redundant Digital/RGB input ,Redundant LED with Multiple Diodes                    |   |                       |                                   |        |
| Dimension & Weight             |                   | (WxHxD) = 1550 x 1151 x 560 mm, Net Weight : Rear CSI = 111 Kg, Front CSI = 133 Kg |   |                       |                                   |        |
| Operating Temperature          |                   | 5°C ~ 40°C (41°F ~ 104°F)  |   |                       |                                   |        |
| Non-Operating Temperature      |                   | -20°C ~ 60°C (-4°F ~ 140°F)  |   |                       |                                   |        |
| Operating / Storage Humidity   |                   | 10% ~ 90%, non-condensing  |   |                       |                                   |        |

Note: \*1. . Through electrical compensation, \*2 Only one of the optional boards can be used with standard input / output board, \*3 Change from 2020/3.

※ All specifications are subject to change without prior notice.

Ver:05.2020

Website: [www.deltadisplays.eu](http://www.deltadisplays.eu) | Contact Us: [info@deltadisplays.eu](mailto:info@deltadisplays.eu)

