



RGB Slim Laser Video Wall


70" Full HD RGB Laser Slim Video Wall

- Rich picture quality with Full HD Resolution for superb image quality
- Ultra High Brightness to give the most vivid colors
- High lumens efficiency for reducing operating costs
- Browser/Server based architecture for quick monitoring
- Slimmest Laser Cube saves real state
-



70" Full HD RGB Laser Slim Video Wall

Delta's Laser Video wall is a rear projection, Laser based Full HD Video wall that offers environment friendly Laser illumination, ultra high brightness and true cube redundancy. Industry's first ultra-bright Laser based DLP® video wall improves energy savings of up to 33%.



LED Light Source



RGB Laser Light Source

Specifications

Model		DVS-708RS DM / DVS-708FS DM					
Description		RGB Laser Light Source Full HD Cube					
Individual Cube Size		70" Diagonal					
Image Size		1550 x 872 mm					
Display Technology		DLP, single chip					
Native Resolution		1920 x 1080 pixels					
Aspect Ratio		16:9					
Screen to Screen Gap		Rear Access : 0.2mm, Front Access : 1.0 mm					
Light Source		Laser (Lasers Class 1)					
Brightness(Bright/High Bright)		Typ. 1800 lumens ^{*1}					
Brightness Uniformity		Up to 95% ^{*2}					
Contrast Ratio		Typ. 1800:1					
Colors		16.7 million					
Color Temperature Range		3200K to 9300K, Custom					
Standard Inputs		1x Digital DVI-I, 2x Digital HDMI, 1x Analog D-sub 15pin, 1x Display Port					
HDMI input support max resolution		3840x2160					
DP input support max resolution		3840x2160					
Standard Outputs ^{*4}		2x Digital HDMI					
HDMI output support max resolution		3840x2160					
Control Options		RS-232 / RS 422, IP, IR					
Screen Brightness	Screen Type	Bright mode	Normal mode	ECO mode	Screen Viewing Angle (1/2 Gain)		
	CSI	520 cd/m ²	370 cd/m ²	250 cd/m ²	H: 36°	V: 34°	
Light source Average Life		60,000 hours	130,000 hours	130,000 hours			
Power Consumption ^{*4}		230 w	180 w	130 w			
Heat dissipation		685 BTU/h	480 BTU/h	340 BTU/h			
Input Voltage		AC 90-240 V @ 50/60 hz					
Noise Level (1m to Screen)		30dB					
Power Supply		Dual Power supply					
Dimension (W x H x D) & Weight		Dimension : 1550 x 1151 x 560 mm, Net weight: Rear = 112Kg, Front = 120Kg					
Operating Temperature		5°C ~ 40°C (41°F ~ 104°F), Operating Altitude : <=4000m					
Non-Operating Temperature (No including Screen)		-20°C ~ 60°C (-4°F ~ 140°F)					
Non-Operating Temperature (Screen)		5°C ~ 40°C (41°F ~ 104°F)					
Operating / Storage Humidity		10% ~ 90%, non-condensing					

Note: ^{*1}. Bright mode Engine brightness, ^{*2}. Through electrical compensation
^{*} All specifications are subject to change without prior notice. Ver:02.2023