



High-bay LED Lighting

Staccato

Durable for long lasting performance

- A robust High-bay luminaire ideal for harsh environment
- Wide or medium beam angle with reduced glare
- DALI dimming control
- Integrated occupancy and daylight sensors
- 10kV surge protection
- Thermal control function to reduce the luminous flux for $T_a > \max$
- Convenient installation with options for hook, bracket or suspension rope
- 5 (+5) years warranty (project specific)

Applications



Factory



Industrial











Transport



Warehouse

www.deltaww-emea.com/ledlighting



	HBEC4H0AE	HBEF4H0AE	HBEB4H0AE	HBEBR4H01AE	HBEBW4H01E
Lumen Output (lm)	20 000	26 200	33 100	42 600	50 200
Power (W)	125	150	200	260	310
Efficacy (lm/W)	160	175	166	164	162
CRI	>80				
CCT	4000K (Other CCT Available: 5000K)				
Operating Temperature	-40° to +65°C				-40° to +50°C
Lifetime	L80B10> 100 000h at Ta=25°C; L80B10> 55 000h at Ta=Max				
Input Voltage	220-240 V				
Beam Angle	100° / 60° / 65° x 100°				100° / 60°
UGR	<25			<27	<28
Ingress Protection	IP66				
Impact Resistance	IK10				
Power Factor	>0.95				
Electrical Safety Class	Class I				
Total Harmonic Distortion	<20%				
Color Tolerance (MacAdam)	3 SDCM				
Weight (kg)	9				
Product Dimension (Ø x H mm)	440 x 181				
Control Interface	DALI				0-10 V
Accessories & options	 Eye bolt MA-01034A (included)  U-Bracket MA-01002A  DC controller MA-01014A  Occupancy sensor MA-01005A				
Photometry					
Dimensions	 				
Remark	The lumen output and efficacy values are given for CCT 4000K (100° beam angle) Thermal foldback feature reduces lumen output for temperatures above Ta Max				

Delta Electronics (Netherlands) B.V.

Zandsteen 15, 2132 MZ Hoofddorp, The Netherlands

E: sleu@deltaww.com

T: +31-20-655-0900