

# 1 kW Wireless Charging System M $\infty$ V<sup>air</sup> 01

Highly efficient wireless charging for industrial applications including electric vehicles and AGVs.

- No part wear
- Fully automated charging
- Low weight on vehicle





## 1 kW Wireless Charging System

#### Versatile Charging

- Charge any battery type
- Each Primary Unit charges 24 V, 36 V and 48 V

a


- CAN bus control or profile charging
- Reliable and silent operation

#### **Easy Integration**

- Compact onboard charging unit
- Intelligent communications
- Power transfer over a 20 mm gap

#### **Wireless Power Transfer**

- Efficiency meets traditional wired chargers
- Safe & unmanned 24/7 operation
- No connector wear
- No maintenance downtime



## **System Overview**

## Specification

Product Line			MOOV <sup>air</sup> 01		
AC Input					
AC Input Rated Voltage			100 to 240 V <sub>AC</sub> 1PH		
AC Input Voltage Range			85 to 265 V <sub>AC</sub>		
AC Input Frequency			50 / 60 Hz (47 to 63 Hz)		
Maximum AC Input Current			12 A		
Power Factor (100% Load)			> 0.95		
Peak Efficiency			92% (24 V version), 93% (36 V and 48 V version)		
Standby Power <sup>1</sup>			< 8 W		
DC Output					
DC Output Nominal Voltage			24 V <sub>DC</sub>	48 V <sub>DC</sub>	36 V <sub>DC</sub>
DC Output Voltage Range			12 to 30 $V_{\text{DC}}$	24 to 60 V <sub>DC</sub>	18 to 45 V <sub>DC</sub>
Maximum Charge Current			41.7 A	20.8 A	27.7 A
Maximum Output Power			1000 W		
Battery Type			Lithium Ion, Lead Acid (AGM / GEL)		
Output Protection			Over voltage, over current, short circuit, reverse connection		
Parallel Operation			Up to 4 systems in CAN mode		
Standby Power <sup>2</sup>			< 2 W		
		Set points from vehicle	CANbus		
Charge Modes		Pre-programmed standalone operation	Multi-stage charge profile		
Environmental Conditio	ns				
Operating Temperature	3		-20 °C to +50 °C (-4 °F to + 122 °F)		
Storage Temperature			-40 °C to +85 °C (-40 °F to + 185 °F)		
Relative Humidity			0% to 95%, non-condensing		
Maximum Operating Altitude			3000 m (9842 ft)		
Shock / Vibration			25 g / 5 g		
Ingress Protection <sup>4</sup>		WPB	IP65		
		WPP and WSP	IP65		
		WSB	IP40		
Mechanical Design					
Pad Air Gap Range			0 mm to 20 mm (0.8 in)		
Maximum Misalignment			20 mm (0.8 in)		
Dimensions (H x W x D)	WPB		192 x 280 x 60 mm (7.6 x 11.0 x 2.4 in)		
	W	PP and WSP	Ø 160 x 19.5 mm (6.3 x 0.8 in)		
	WSB		168 x 82 x 28 mm (6.6 x 3.2 x 1.1 in)		
Cable Length (WPU)	WPP		1120 mm (44.1 in) typical		
Cable Length (WSU)	DC Output		500 mm (19.7 in)		
	Signals		100 mm (1.97 in)		
	WSP		380 mm (15 in)		
Weight	WPB and WPP		5.4 kg (11.9 lb)		
Weight	WSB and WSP		1.5 kg (3.3 lb)		
Cooling	WPB		Natural convection		
Cooling	W	SB and WSP	Contact		
Status LEDs			WPB		

Approvals and Compliance	USA / Canada	Europe
Safety marks	cDEKRAus	CE
Safety	UL 60950-1 / UL 62368-1 CAN/CSA C22.2 no. 60950-1 / no. 62368-1	EN 60950-1, EN 62368-1
EMC	FCC 15B, 18B, ICES-003, RSS-216, Class A <sup>4</sup>	ETSI EN 301 489-1, ETSI EN 301 489-17, EN 55011, EN 61000-6-4, EN 61000-6-2, Class A <sup>4</sup>
RF	FCC Part 15.247, FCC Part 15.209, RSS-247	ETSI EN 300 328
EMF	EN 62311, IEEE C95.3	·

1 WPB connected to AC but not charging

2 Secondary Unit connected to battery and not charging

3 Derating above 40 °C 4 Class B available on request



### Delta Energy Systems (Germany) GmbH

Tscheulinstrasse 21, 79331 Teningen E-mail: IEV.sales@deltaww.com

www.deltaww.com



October 2024 Revision 3.1 © Copyright – Delta Energy Systems (Germany) GmbH – All rights reserved. All information and specifications can be modified without prior notice.