



## Landscape Lighting

# GLHA Series

Modularized design for easy upgrade

- Whole structure heating dissipation design with best thermal conduction and radiation.
- Fully modularized UV stabilized PC lens, IK09 rating
- Life span of LEDs used in the Luminaire shall be more than 50,000 hours at 70% light output
- 10KV surge protection capabilities for luminaires

### Applications



Roadway



Public areas



Park

	BA-GLHA26NLAMB0	BA-GLHA26YLAMB0	BA-GLHA60YLAMB0	BA-GLHA26Y2S1B0	BA-GLHA60Y2S1B0
Output Lumen	3640 lm	3640 lm	7500 lm	3640 lm	7500 lm
Rated Voltage	110/220Vac, 50/60Hz				
Efficiency	140lm/W	140lm/W	125lm/W	140lm/W	125lm/W
Power consumption	26	26	60	26	60
CRI (Ra)	>70				
CCT (K)	5000K	3000K			
Operation Temperature	-40~50 °C				
Power Factor	> 0.95				
IP Grade	IP66				
Lifetime	L70>50,000hrs				
Compliance	CNS14335/ CNS15015				
Weight	6Kg				
Photometric					
Dimension					



台北市內湖區瑞光路186號  
電話: + 886 2 8797 2088  
傳真: + 886 2 6606 3308  
email: LS.Sales@deltaww.com



buildings.deltaww.com

All specifications are subject to change without notice. Copyright © Delta Electronics, Inc. All rights reserved.

GLHx Series\_cht\_202301