



Linear LED Lighting 藍牙線性條燈 Delta IoT Lighting Solution

- 內建藍牙 BLE5.0 無線控制傳輸裝置
- 發光效率 152 lm/W
- 模組化設計，易於安裝維修
- 可選配藍牙定位或連結外部藍牙紅外線感應器

應用場域



停車場





走廊



倉庫、賣場



工廠

型號	BA-ST425NH1B
額定光通量	3,500 lm / LED模組 19Wx1
輸入電壓	AC 110-277V
總消耗功率	23 W
額定發光效率	152 lm/W
演色性	≥ Ra 80
色溫	5,000K
功率因素	≥ 0.9
總諧波失真 THD	< 20%
待機功率	< 0.5W
調光輸出範圍	1~100%
無線控制	Bluetooth Profile: SIG Mesh Profile / Bluetooth Specification: 5.0
燈具外殼材質	聚碳酸酯(燈罩) / 冷軋鋼板白色烤漆(電源室外殼)
防水等級	IP20 (乾燥與潮濕環境)
使用環境溫度	-20°C / +50°C
壽命	> 50,000 hrs L80/B10
固定方式	表面固定 / 懸吊
配件	表面固定螺絲組 / 懸吊組 (選購)
重量	1.4kg
尺寸	 Technical drawing of the BA-ST425NH1B light fixture. The top view shows a rectangular fixture with a length of 1210.6 mm and a width of 66.8 mm. The side view shows a height of 58.4 mm and a mounting bracket width of 61.0 mm. A detail view of the mounting bracket shows a width of 117.8 mm and a height of 30 mm.
安規	符合歐盟CE規範 固定式燈具安全性標準 EN IEC 60598-1 電磁相容性標準 EN IEC 55015 藍光危害標準 IEC TR 62778
配光曲線	 Beam spread diagram showing light distribution. The diagram is a circular plot with concentric circles representing beam angles. The outermost circle is labeled 125° and the innermost circle is labeled 110°. The plot shows the light distribution pattern for the fixture.
發光角度 (1/2強度)	125°(垂直) / 110°(水平)