



High-bay LED Lighting

Legatto Compact

Compact design with integrated lighting control

- Ultimate reliability with compact housing and very long lifetime
- Saves energy and maintenance costs
- Wide or medium beam angle with reduced glare
- 0-10V (standard) and DALI (optional) dimming control
- Possible to integrate occupancy and daylight sensors
- Thermal control function to reduce the luminous flux for $T_a > T_{max}$
- Convenient installation with options for hook and bracket
- 5 years warranty

Applications



Logistic
Centers



Warehouse



General
Manufacturing

















Exhibition
Halls



Transport

www.deltaww-emea.com/ledlighting



	SCDB84H00E	SCDB84600E	SCDBD4H00E	SCDBD4600E	SCDBI4H00E	SCDBI4600E														
Lumen Output (lm)	12 400	11 400	18 300	16 900	21 900	20 200														
Power (W)	85		130		160															
Efficacy (lm/W)	146	134	141	130	137	126														
CRI	>80																			
CCT	4000K (Other CCT Available: 5000K)																			
Operating Temperature	- 40° to +55°C																			
Lifetime	L80B10> 100 000h at Ta=25 °C; 50 000h at Ta=Max																			
Input Voltage	220-240 V																			
Beam Angle	100°	60°	100°	60°	100°	60°														
UGR	<25	<19	<25	<22	<25	<22														
Ingress Protection	IP65																			
Impact Resistance	IK10																			
Power Factor	>0.9																			
Electrical Safety Class	Class I																			
Compliance	<20%																			
Color Tolerance (MacAdam)	3 SDCM																			
Weight (kg)	3.5																			
Product Dimension (Ø x H mm)	347 x 216																			
Max luminaires in one loop	DALI /0-10 V																			
Accessories & options	<table border="0"> <tr> <td>U-Bracket MA-01021A</td> <td>Occupancy sensor MA-01012A</td> <td>DC controller MA-01014A</td> <td>Diffuser MA-01018A</td> <td colspan="3"></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td colspan="3"></td> </tr> </table>						U-Bracket MA-01021A	Occupancy sensor MA-01012A	DC controller MA-01014A	Diffuser MA-01018A										
U-Bracket MA-01021A	Occupancy sensor MA-01012A	DC controller MA-01014A	Diffuser MA-01018A																	
																				
Photometry																				
Dimensions																				
Remark	The given lumen output and efficacy values are given for CCT 4000K Thermal foldback feature reduces lumen output for temperatures above Ta=Max																			