



Industrial LED Light Stratus

- Multi-lumen with power adjustable
- High efficiency up to 160 lm/W
- Repairable with easy maintenance
- Through-wiring for linking luminaires
- Tool-free and fast installation
- PIR & Microwave sensor available
- 5 years warranty

Applications



Commercial



Industrial



Transport



Warehouse

www.deltaww-emea.com/ledlighting



	LSHD04STR4240	LSHD04STR5440
Type of Product	Industrial Application	
Product variation (mm)	1200	1500
Lumen Output (lm)	3520 / 4800	4480 / 6400
Input Voltage (V)	AC220/240V 50/60Hz	
Power (W)	22/30	28/40
Efficacy (lm/W)	160	
CRI (Ra)	> 80	
CCT (K)	4000K (Other CCT Available: 3000K, 5000K, 6500K)	
Power Factor	> 0.9	
Operating Temp (°C)	-20°C to +40°C	
Lifetime	100,000 Hrs L80/B10	
Protection	IP65 / IK08	
Warranty	5 years	
Beam Angle	150°	
Weight (kg)	0.68	0.8
Dimensions (mm)		
Standard accessories	Ceiling mounting brackets (2 pcs)	
Remarks	<p>All values are based on 4000K CRI80 and in +25 °C ambient temperature, luminous flux tolerance +-5%, output power tolerance +-5%.</p> <p>Caution: The LED luminaire is only allowed to be applied to indoor neutral environment. Any severe environment application including high/low temperature, high humidity, high salinity, high-ammonia etc..is not permitted without the official confirmation from the manufacturer.If any misapplication happens, the warranty policy is no longer guaranteed.</p>	

Accessories			Photometry
<p>STRATUS DRIVER LSHD04STR0015/16</p>	<p>STRATUS 1200 4000K PCB LSHD04STR0010</p>	<p>STRATUS 1500 4000K PCB LSHD04STR0011</p>	
<p>STRATUS MOTION SENSOR LSHD04STR0012</p>	<p>STRATUS PIR SENSOR LSHD04STR0013</p>	<p>STRATUS REMOTE CONTROL LSHD04STR0014</p>	

Specifications are subject to change without notice.