

# OutD M Series

## Outdoor Cabinet



OutD “M” series outdoor cabinets are the new series of the new modular cabinets. Modular construction of the cabinet is very user friendly. Many parts like door, back wall, side walls and roof can be opened, demounted or removed on site to make the installation of the customer equipment as easiest and as most comfortable as possible. Cabinet is designed with two types of cooling system: AV (air ventilation) and AV + A/C (hybrid: air ventilation + air conditioner).

### Key Features

- Dimensions:
  - OutD1.8M: W770 x H1827 x D852
  - OutD2.0M: W870 x H2050 x D952
- Material: aluminium/HDG frame + HDG steel panels (optional aluminum)
- IP 55 protection
- Panels with optional thermal insulation
- Different cooling equipment
  - AV (LENI concept)
  - Hybrid AV + A/C
- Rear door possibility
- Side panels removable
- Cabinet would be send assembled or flat packed

### Applications

- 3G / 4G / 5G
- Fixed Line
- Datacom



# OutD M Series



GOCACS-01-ZL

## MECHANICAL

	OutD 1.8M	OutD 2.0M
Dimensions (W x H x D) (overall)	770 x 1827 x 852mm (30.31 x 71.92 x 33.54in)	870 x 2050 x 952mm (34.25 x 80.70 x 37.48in)
Dimensions (W x H x D) (for hybrid version)	770 x 1827 x 986mm (30.31 x 71.92 x 38.81in)	870 x 2050 x 1086mm (34.25 x 80.70 x 42.75in)
Total User Space	19" 35U	19" 40U
Cabinet Plinth	Included, H=150mm	
Weight	150kg (330.69lb)	
Construction	Multi-layer HDG Steel, Thickness: 1.25mm	
Isolation	20mm EPS100-038	
IP Protection	IP55	
Impact Protection	IK10	
Locking Mechanism	Prepared for half cylinder. (Lock provided by customer)	
Cable Entry	Entry point: Bottom Type: PG16 x2, PG21 x6, PG29 x1; MC25 x2	
Plinth Cable Entry	Bottom, rear and side access	

## ENVIRONMENTAL

Ambient temperature	-25 to +55 °C (-13 to +131 °F)
Inside temperature	+5 to +55 °C (+41 to +131 °F)
Cooling	Cooling type: Fans, Air conditioning Fan type: EFB1748VHG (2 pcs) Fan control: Delta controller
Air Filter	G3 (for AV); G4 or M5 (for HYB)

\* All specifications are subject to change without prior notice.

### Delta Electronics Inc.

3 Tungyuan Road, Chungli Industrial Zone,  
Taoyuan City 32063, Taiwan.

T +886 3 452 6107 / F +886 3 452 7314

[www.deltaww.com](http://www.deltaww.com)

