

DK02S/D SERIES

2W DC/DC CONVERTER, DIP Package, High Isolation



FEATURES

- Efficiency up to 75%
- Standard DIP-16 Package
- Reinforced Insulation rated for 300VAC Working Voltage
- High Isolation Voltage 4000VAC
- Operating Temperatue Range –25°C to +80°C
- Low isotation Capacitance
- Low Leakage Current
- Lead free, RoHs Compliant
- 3 Years Product Warranty

The DK02S/D series are miniature, DIP Package, isolated 2W DC/DC converters with ultra- high 4,000VAC isolation. It offers low leakage current and allows a wide operating temperature range of -25°C to +80°C. These isolated DC/DC converters are the latest offering from a world leader in power systems technology and manufacturing — Delta Electronics, Inc. With creative design technology and optimization of component placement, these converters possess outstanding electrical and thermal performance, as well as extremely high reliability under highly stressful operating conditions

Model Lis	t								
Model	Input	Output	Output	Dutput Current Input Current		Load	Max. Capacitive	Efficiency	
Number	Voltage	Voltage						Load	(typ.)
	(Range)		Max.	Min.	@Max. Load	@No Load			@Max. Load
	VDC	VDC	Ма	Ma	Ma(typ.)	Ma(typ.)	% (max.)	Uf	%
DK02S0505A		5	400	8	606		12		66
DK02S0512A	F	12	165	3	600		10	330	66
DK02S0515A	5 (4.5 ~ 5.5)	15	133	2.5	605	60	10		66
DK02D0512A	(4.5 ~ 5.5)	±12	±83	±1.5	553		10	100*	72
DK02D0515A		±15	±66	±1	542		10		73
DK02S1205A		5	400	8	253		12	330	66
DK02S1212A		12	165	3	250		10		66
DK02S1215A	12 (10.8 ~ 13.2)	15	133	2.5	252	30	10		66
DK02D1212A	(10.0 ~ 13.2)	±12	±83	±1.5	224		10	100*	74
DK02D1215A		±15	±66	±1	220		10	100*	75
DK02S2405A		5	400	8	126		12		66
DK02S2412A		12	165	3	125		10	330	66
DK02S2415A	24 (21.6 ~ 26.4)	15	133	2.5	126	15	10		66
DK02D2412A	(21.0 ~ 20.4)	±12	±83	±1.5	112	1	10	400*	74
DK02D2415A		±15	±66	±1	110		10	100*	75

* For each output



Input Characteristics						
Parameter	Model	Min.	Тур.	Max.	Unit	
	5V Input Models	4.5	5	5.5		
Input Voltage Range	12V Input Models	10.8	12	13.2		
	24V Input Models	21.6	24	26.4	VDC	
	5V Input Models	-0.7		9	VDC	
Input Surge Voltage (1 sec. max.)	12V Input Models	-0.7		18		
	24V Input Models	-0.7		30		
Reverse Polarity Input Current				0.3	А	
Input Filter	All Models	Internal Capacitor				
Internal Power Dissipation				650	Mw	

Output Characteristics								
Parameter	Conditions	Min.	Тур.	Max.	Unit			
Output Voltage Accuracy			±2.0	±4.0	%			
Output Voltage Balance	Dual Output, Balanced Loads		±0.1	±1.0	%			
Line Regulation	Vin=Min. to Max.		±1.2	±1.5	%			
Load Regulation	lo=20% to 100%	See Model Selection Guide						
Ripple & Noise (20MHz)			100	150	Mv _{P-P}			
Ripple & Noise (20MHz)	Over Line, Load & Temp.			200	Mv _{P-P}			
Ripple & Noise (20MHz)				15	Mv rms			
Temperature Coefficient			±0.01	±0.02	%/°C			
Short Circuit Protection		0.5 Second Max.						

Isolation and Safety Standards									
Parameter	Conditions	Min.	Тур.	Max.	Unit				
I/O Isolation Voltage (rated)	60 Seconds 4000				VACrms				
I/O Isolation Test Voltage	Flash tested for 1 Second	6000			V _{PK}				
Leakage Current	240VAC, 60Hz			2	Ua				
I/O Isolation Resistance	500 VDC 10				GΩ				
I/O Isolation Capacitance	100KHz, 1V		15	20	Pf				
	Cul/UL60950-1, CSA C22.2 No. 60950-1-03								
Safety Standards	UL60601-1,CSA C22.2 No.601-1								
	IEC/EN 60950-1, IEC/EN 60601-1								
A	IEC60950-1 CB report, Cul/UL 60950-1 certificate								
Approvals	UL60601-1 UL certificate								


General Characteristics									
Parameter Conditions Min. Typ. Max.									
Switching Frequency		50	80	100	KHz				
MTBF (calculated)	MIL-HDBK-217F@25°C, Ground Benign	2,000,000			Hours				

Recommended Input Fuse		
5V Input Models	12V Input Models	24V Input Models
1000Ma Slow-Blow Type	500Ma Slow-Blow Type	200Ma Slow-Blow Type

Environmental Characteristics									
Parameter	Conditions	Min.	Max.	Unit					
Operating Temperature Range (with Derating)	Ambient	-25	+80	°C					
Case Temperature			+90	C°					
Storage Temperature Range		-50	+125	C					
Humidity (non condensing)			95	% rel. H					
Cooling	Free-Air convection								
Lead Temperature (1.5mm from case for 10Sec.)			260	C°					




Power Derating Curve



Notes

- 1 Specifications typical at Ta=+25°C, resistive load, nominal input voltage and rated output current unless otherwise noted.
- 2 Ripple & Noise measurement bandwidth is 0-20MHz.
- 3 These power converters require a minimum output loading to maintain specified regulation, operation under no-load conditions will not damage these modules; however they may not meet all specifications listed.
- 4 All DC/DC converters should be externally fused at the front end for protection.
- 5 That "natural convection" is about 20LFM but is not equal to still air (0 LFM).
- 6 Specifications subject to change without notice.

Mechancial Drawings



Physical Outline

Case Size	: 23.8x13.4x8.6mm (0.94x0.53x0.34 Inches)	
Case Material	: Non-Conductive Black Plastic (flammability to UL 94V-0 rated)	
Weight	: 5.1g	



Part Numbering System

D	К	02	S	05	05	А			
Form factor	Family series	Watt	Number of Outputs	Input Voltage	Output Voltage	Option Code			
D - DIP	A~Z	01 : 1W	S - Single	03 : 3.3V	03 : 3.3V	A - Std. Functions			
P - SIP		02 : 2W	D - Dual	05 : 5V	05 : 5V				
S - SMD		03 : 3W		12 : 12V	12 : 12V				
		04 : 4W		15 : 15V	15 : 15V				
		06 : 6W		24 : 24V	24 : 24V				

WARRANTY

Delta offers a three(3) years limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.