



50" Ultra Slim DLP Video Wall Cubes


Product Features

- Space-Saving Design
- Long-Lasting LED Light Engine
- Superior Color Uniformity
- Six-Axis Adjustment For Perfect Alignment
- Auto Color Calibration
- Advanced Optical & Screen Design
- Redundant Power Supply Module
- Wireless Diagnostics and Control
- Motorized 6-Axis Adjustment
- Auto Geometry Alignment For Quick Installation

www.deltadisplays.com



DELTA
Smarter. Greener. Together.



Specifications

Model				DVS-5080S9 DO CB			
Display Capabilities							
Native Resolution		FHD , 1,920 x 1,080					
Display Technology		1-Chip DLP					
Brightness on screen (nits)		FXS				Eco	434
						Normal	527
						Bright	582
Dynamic Contrast		1,200,000 : 1					
White Point		3,200K, 6,500K, 7,500K and 9,300K					
Uniformity		> 96%					
Screen							
Screen Dimension (W X H)		1,107.0 x 623.0 mm					
Screen Type		FXS Screen					
Screen Gap		< 0.1 mm					
Color Stability		Self Calibrating With Color Sensor					
Half Gain Angle (H/V)							
Horizontal		34° (+/- 3°)					
Vertical		33° (+/- 3°)					
Light Source							
Lamp Type		LED (RGB) , 6 x Redundancy for Each of 3 LED's					
Estimated Lamp Life		> 60,000 hrs, > 100,000 hrs (eco)					
Operation							
Operating Temperature		5°C - 40°C (41°F - 104°F)					
Non-operating Temperature		-20 °C - 60 °C (-4°F - 140°F)					
Humidity		10% - 90%, Non-condensing					
Power Requirement							
Input Voltage		AC 90 - 240V @50/60Hz					
Consumption (Eco, Typ, Max)		150W, 225W, 270W					
Mechanical							
Dimensions (W x H x D)		1,108.0 x 868.4 x 600.0 mm (43.6 x 34.2 x 23.6")					
Weight		Rear Access < 50 KG (110 lb)					
Interface							
Standard Inputs		Analog D-sub 15pin				Digital DVI-I	
		HDMI				Component Video BNC	
		CVBS BNC				5BNC (RGBHV or YPbPr)	
Optional Inputs		Display Port				3G-SDI	
		S-Video					
Standard Outputs		Digital DVI-D					
Input Frequency		24 – 62 Hz					
Signal Processing		Loop-Through (DVI, CVBS) Free Scaling					
Selective Option		DVSWeb Control System Software					
		Redundancy Power Supply Module					
		Auto Color Sensor Module					
		Motorized 6-Axis Adjustment					
Control							
Communication		RS-232 Port				RS-422 Port	
		IR Receiver				RJ-45 Ethernet	

*All specifications are subject to change without prior notice.

Ver: 03. 2014

Delta Group website :

www.deltaww.com

Product website :

www.deltadisplays.com

Contact E-mail :

VW.Sales@deltadisplays.com

Europe

FRANCE

Delta Electronics (France) S.A.
ZI du bois Chaland 2 15 rue des
Pyrénées, Lisses, 91056 Evry
Cedex, France

NETHERLANDS

Delta Electronics Europe
Zandsteen 15, 2132 MZ
Hoofddorp,
The Netherlands

SLOVAKIA

Delta Electronics (Slovakia) s.r.o.
Priemyselna ulica 4600/1
018 41 Dubnica nad Vahom,
Slovakia

North America

USA/ FREMONT

Delta Products Corporation
4405 Cushing Parkway,
Fremont, CA 94538, U.S.A.

USA/ PORTLAND

Delta Products Corporation
1600 NW Compton Drive,
Suite 100, Beaverton OR 97006,
U.S.A.

Asia

TAIWAN

Delta Electronics, Inc.
186 Ruey Kuang Road, Neihu,
Taipei 11491, Taiwan

KOREA

Delta Electronics (Korea) Inc.
234-9, Duck soo Building 7F,
Nonhyun-dong, Kangnam-Gu,
Seoul, Korea 135-010

JAPAN

Delta Electronics (Japan) Inc.
Delta Shibadaimon Building,
2-1-14 Shibadaimon, Minato-Ku,
Tokyo, 105-0012, Japan

THAILAND

Delta Electronics (Thailand) PCL.
909 Soi 9, E.P.Z., Bangpoo
Industrial Estate, Moo 4, Pattana
1 Rd., T.Prakasa, A.Muang
Samutprakarn 10280, Thailand

INDIA

Delta India Electronics Pvt. Ltd.
Plot No 43, Sector 35, HSIDC,
Gurgaon 122001, Haryana,
India

CHINA

Delta Electronics (Jiang Su) Ltd.
1688 Jiangxing East Road,
Wujiang
Economic Development Zone,
Wujiang City, Jiang Su
Province, China

SINGAPORE

Delta Electronics (Singapore)
1, Kaki Bukit Road 1, #03 -29,
Enterprise One, Singapore
415934

