



FEATURES

- ♦ Ultra wide input voltage range, 18~106V
- ♦ 200W Output @ 18V~27V Vin range
- ♦ 300W Output @ 27~106V Vin range (Including 27V)
- ♦ Full Load Efficiency up to 91.0% @48Vin
- ♦ Integrated fuse holder
- ♦ Parallel Connection of multiple units
- ♦ Box type package with metal base plate
- ♦ Package Dimension:
190.0x76.0x44.0mm (7.48"x2.99"x1.73")
- ♦ Operating Temperature Range - 40°C to +75°C
- ♦ Input Reverse Polarity Protection
- ♦ Minimized Inrush current
- ♦ Input UVLO, Output OCL, SCP, OVP, OTP
- ♦ Enable on/off (option)
- ♦ 2250VDC Isolation
- ♦ IP67 protection for selective model
- ♦ RoHS Compliant
- ♦ ISO 9001, ISO 14001 certified manufacturing facility
- ♦ UL60950
- ♦ CE Mark
- ♦ EMC compatible: EN12895, CISPR11 ClassA
- ♦ Electrical transient conduction: ISO7637-2

The B62SR24125, a ultra wide input voltage range of 18~106V, and single isolated output converter, is the latest product offering from a world leader in power systems technology and manufacturing — Delta Electronics, Inc. Such box type DCDC converter can provide 300W (200W at Vin < 27V), 24.5V regulated DC output voltage with full load efficiency up to 91.0% @48Vin; The B62SR24125 offers input UVLO, output over current limit, short circuit, output over voltage, over temperature, and input reverse polarity protections. It has an option for intergrated fuse holder and enable on/off function. It also has parallel function; and allows a wide operating temperature range of -40°C to +75°C. With creative design technology and optimization of component placement, this converter possess outstanding electrical and thermal performance, as well as high reliability under extremly harsh operating conditions. The B62SR24125 meets IP67 protecion (refer to "water protection level" specification).

INPUT CHARACTERISTICS

Item	Condition	Min.	Typ.	Max.	Unit
Continuous Input Voltage		18	48	106	VDC
Max Input voltage	10 minutes, normal operating			126	VDC
Input Under-Voltage Lockout, Turn-On Voltage Threshold		16	17	18	VDC
Input Under-Voltage Lockout, Turn-Off Voltage Threshold		14	15	16	VDC
Lockout Hysteresis Voltage		1	2	3	VDC
Maximum Input Current	Vin=18V, 100% Load		13.0	13.5	A
No-Load Input Current	Vin=24V		180	220	mA
	Vin=48V		80	120	mA
	Vin=72V, 80V		50	100	mA
Off converter input current	Vin=48V		15	25	mA
Reflected input ripple current	Vin=48V, Vpp			0.6	A
Max Reverse Polarity Input Voltage				106	VDC
Max Inrush current				10	A
Internal Input Fuse	Ø6.35mm*31.75mm	250V/30A Fast-acting fuse			

OUTPUT CHARACTERISTICS					
Item	Conditions	Min.	Typ.	Max.	Unit
Operating Output Current Range	Vin=18V~27V	0		8	A
	Vin=27V~106V(include 27V)	0		12.5	A
Output Voltage Set Point	Total Vin range, Io=0	24.8	25.0	25.2	V
	Vin=18~27V, Io=8A	24.5	24.7	24.9	V
	Vin=27~106V, Io=12.5A	24.3	24.5	24.7	V
Output Voltage Ripple and Noise,	Full load, Vpp, 20MHz bandwidth		50	100	mV
	RMS		20	50	mV
Output Current Limit	Vin=24V	9	10	12	A
	Vin=36V, 48V, 72V, 80V	13	15	17	A
Current share accuracy	Vin=48V, 24A for each module		6	10	%
Start-up time(start _up time by Vin)	Vin= 48V(for A/B/C/D)		700	1000	mS
	Vin=72V(for A/B/C/D)		850	1200	mS
Start-up time(start _up time by Enable)	Vin= 48,72V(for C)		250	400	mS
Rise time			60	100	mS
Output Voltage Protection		26	27	28	V
Output Voltage Current Transient, positive and negative voltage step	Vin=24V, 4A to 6A, 0.1A/us slew rate		150	250	mV
	Vin=27~106V. 6.25A to 9.375A, 0.1A/us slew rate		150	250	mV
Maximum Output Capacitance	ESR>10mohm			2000	μF
Output overshoot				3	%
Efficiency @ 100% Load(8A)	Vin=24V	86.5	88.5		%
Efficiency @ 100% Load(12.5A)	Vin=36V	87.5	89.5		%
Efficiency @ 100% Load(12.5A)	Vin=48V	89.0	91.0		%
Efficiency @ 100% Load(12.5A)	Vin=72V,80V	90.0	92.0		%
Efficiency @ 60% Load(4.8A)	Vin=24V	86.0	88.0		%
Efficiency @ 60% Load(7.5A)	Vin=36V	88.0	90.0		%
Efficiency @ 60% Load(7.5A)	Vin=48V	89.5	91.5		%
Efficiency @ 60% Load(7.5A)	Vin=72V,80V	90.0	92.0		%
GENERAL CHARACTERISTICS					
Item	Conditions	Min.	Typ.	Max.	Unit
Isolation Voltage,	Input to Output, Input to Case			2250	VDC
	Output to Case			550	VDC
Isolation Resistance, Input to Output		10			MΩ
Isolation Capacitance, Input to Output			7000		pF
Switching Frequency			160		KHz
MTTF			131400		Hours
Weight			900		g
ENVIRONMENTAL SPECIFICATIONS					
Parameter	Conditions	Min.	Max.	Unit	
Storage Temperature Range		-40		+125	°C
Operating Temperature Range	Ambient Temperature	-40		+75	°C
Over Temperature Protection	NTC Temperature		118		°C
Humidity (non condensing)				95	% rel. H
Water Protection Level	For model P/N with suffix B		IP67		
Vibration	IEC 60068-2-6	10G/15~200HZ/3 PLANES			
Shock	IEC 60068-2-27	50G 3 PLANES			
Emission	EN12895	30-1000MHz 34-45dBuV/m			
Immunity	EN12895, EN61000-4-3	10V/m /27-1000MHz AM; 10V/m /900MHz PM			
ESD	EN12895, EN61000-4-2	Direct: ±2KV ±4KV; Air: ±2KV ±4KV ±8KV			
NOTES					
1	Specifications typical at Ta=+25°C, nominal input voltage and rated full load output current unless otherwise noted.				
2	Specifications are subject to change without notice.				
3	The module can meet IEC61000-4-3 immunity criteria A at 20V/m /80-1000MHz				




Figure 1: Efficiency vs. Output current
V_{in}=24V,36V,48V, 72V, 80V




Figure 2: Loss vs. Output current
 @ *V_{in}=24V,36V,48V, 72V, 80V*




Figure 3: Dynamic response to load step 6.25A~9.375A
 with 0.1A/uS slew rate at 48V_{in}
 CH1:VOUT, 200mV/div, 500uS/div




Figure 4: Vout start up with Vin on at 48V_{in}, 12.5A I_{out},
 TOP: VIN, 20V/div, 200mS/div
 BOTTOM: VOUT, 10V/div, 200mS/div




Figure 5: Output ripple & noise at 48V_{in}, 12.5A I_{out}
 CH1:VOUT, 50mV/div, 2uS/div




Figure 6: Output over voltage protection at 48V_{in}, 6.25A I_{out}
 CH1:VOUT, 10V/div, 50mS/div

ELECTRICAL CURVES (CONTINUOUS)




Figure 7: Input current vs. Input voltage
@ $V_{in}=18V\sim 27V$, 200W; $V_{in}=27V\sim 106V$, 300W




Figure 8: Output voltage vs. Output current
OCL Performance




Figure 9: Output voltage vs. Output current
@ $V_{in}=48V$. Droop function.




Figure 10: Current share accuracy vs. Total output current
2 in parallel.




Figure 11: Inrush current @ $V_{in}=48V$
CH1:lin, 2A/div, 200nS/div; Max current 2.7A, $I_2t=1.24E-7$
 A^2S

FEATURES DESCRIPTIONS

Output Over-Current Limit and Short Protection

The modules include internal output over-current limit (OCL) and short circuit protection (SCP) circuits, the OCL set point is lower than that of the SCP; The response of SCP circuit is much fast than that of the OCL circuit. The slowly increase of the output current will let module enter OCL protection when the current exceeds the OCL set point, while the fast increase of the output current will let module enter SCP when the current exceeds the SCP set point.

When the modules enter OCL protection, the output voltage will decrease while the output current is kept constant, the output voltage will soft start to set point when the overload condition is removed.

The module will enter hiccup mode when it triggers the SCP set point. The module will try to restart after shutdown. If the overload condition still exists, the module will shut down again. This restart trial will continue until the overload condition is removed.

Output Over-Voltage Protection

The power module includes an internal output over-voltage protection(OVP) circuit, which monitors the voltage on the output terminals. If this voltage exceeds the OVP set point, the module will shut down, and then restart after a fixed delay time (hiccup mode), please refer to figure6 for detail.

Over-Temperature Protection

The over-temperature protection consists of circuitry that provides protection from thermal damage. If the temperature exceeds the preset temperature threshold the module will shut down and enter into latch mode, and all components will not exceed their absolute maximum temperature ratings. The module will not recover until the input source is powered on again.

Remote On/Off

B62SR24125C has Enable control function. This Enable PIN is designed on the primary side of converter, the converter will turn on when the Enable PIN connected to VIN+, and turn off when the Enable PIN connected to VIN- or floating.

Enable logic	Notes and Condition	Min.	Typ.	Max.	Unit
1 Enable logic	For C	14			V
2 Enable logic	For C			5	V
3 Enable input pull down resistor ($I=V_{in}/R$)	For C	300k		400k	ohm




Figure 12: suggested Enable connection

Input Reverse Voltage Protection

The input reverse voltage protection is provided by an diode on the input line, the standoff voltage for the reverse protection shall be no less than -106V.

Input Voltage Transient Note

The module contains two stage: Boost and half bridge (Figure 13). Boost stage will be bypassed when $V_{in} > 63V$ (tolerance: 60~66V). The boost re-start time is about 200mS. Therefore, please carefully when input voltage transient down across 60~66V. The output voltage may occur overshoot and re-start in this case. Please contact Delta if you need use it in this case and can't accept re-start.




Figure 13: Block Diagram

Parallel Connection of Multiple Units

Two units' parallel operation is verified, please contact Delta if more than two units need to be paralleled. While paralleling multiple units, the impedance of the cables from unit to junction point of each unit should be within $\pm 5\%$ of each other.




Figure 13: Suggested Parallel Connections

EMC

The converter has the internal EMI filters and meet the EMC standards EN12895 30-1000MHz 34-45dBuV/m. The test result is showed as below.

Conditions: Vin=48V, Io=12.5A, 10m measure distance




Figure 14: Test Result (Vertical)




Figure 15: Test Result (Horizontal)

Fuse Replacement

For the versions with the intergrated the fuse holder, when the fuse needs to be replaced, it can be taken down in an anticlockwise direction by slotted type screwdrivers.

Recommended fuse replacement P/N: Littlefuse 0314030.MXP

THERMAL CONSIDERATION

The thermal curve (Figure17~21) is based on a 250x300x5 AL table, shown as below figure.




Figure 16: Thermal consideration

THERMAL CURVES




Figure 17: Output Current vs. Ambient temperature @ Vin=24V




Figure 18: Output Current vs. Ambient temperature @ Vin=36V




Figure 19: Output Current vs. Ambient temperature @ Vin=48V




Figure 20: Output Current vs. Ambient temperature @ Vin=72V




Figure 21: Output Current vs. Ambient temperature @ Vin=80V

THERMAL CONSIDERATION

The following figure shows the location to monitor the temperature of base plate. Before customer decides to use this DCDC converter, a thermal evaluation need to be done to make sure the temperature of base plate is lower than that read from below thermal curves (Figure23~27 base on different input voltage).




Figure 22: Thermal consideration

THERMAL CURVES




Figure 23: Output Current vs. Base Table temperature @ Vin=24V




Figure 24: Output Current vs. Base Table temperature @ Vin=36V




Figure 25: Output Current vs. Base Table temperature @ Vin=48V




Figure 26: Output Current vs. Base Table temperature @ Vin=72V






Figure 27: Output Current vs. Base Table temperature @ Vin=80V

MECHANICAL DRAWING



Pin Connections	
Pin	Function Description
1	OUTPUT -
2	OUTPUT +
3	INPUT -
4	INPUT +

- All dimensions in mm (inches)
- Tolerance: X.X±0.5 (X.XX±0.02)
X.XX±0.25 (X.XXX±0.010)
- Connector:
MOLEX MINI-FIT Sr™ Header
(MOLEX P/N :42819-4213)




Pin Connections	
Pin	Function Description
1	OUTPUT -
2	OUTPUT +
3	INPUT -
4	INPUT +

- All dimensions in mm (inches)
- Tolerance: X.X±0.5 (X.XX±0.02)
X.XX±0.25 (X.XXX±0.010)
- Connector:
MOLEX MINI-FIT Sr™ Header
(MOLEX P/N :42819-4213)
- Connector kit :
Housing: 42816-0412
Terminal: 42815-0042

MECHANICAL DRAWING


Mechanical Dimensions

Pin Connections



Pin	Function Description
1	OUTPUT -
2	OUTPUT +
3	INPUT -
4	INPUT +


- All dimensions in mm (inches)
- Tolerance: X.X±0.5 (X.XX±0.02)
X.XX±0.25 (X.XXX±0.010)
- Connector:
Deutsch DTP Receptacles
(DEUTSCH P/N :DTP04-4P)




Pin	Function Description
1	OUTPUT -
2	OUTPUT +
3	INPUT -
4	INPUT +

- All dimensions in mm (inches)
- Tolerance: X.X±0.5 (X.XX±0.02)
X.XX±0.25 (X.XXX±0.010)
- Connector:
Deutsch DTP Receptacles
(DEUTSCH P/N :DTP04-4P)
- Connector kit :
Housing: DTP06-4S
Wedge lock: WP-4S
Terminal: 0462-203-12141

MECHANICAL DRAWING

Mechanical Dimensions		Pin Connections	
		Pin	Function Description
		1	OUTPUT -
		2	OUTPUT +
		3	INPUT -
		4	INPUT +
5	ENABLE		
		<ul style="list-style-type: none"> ➤ All dimensions in mm (inches) ➤ Tolerance: X.X±0.5 (X.XX±0.02) X.XX±0.25 (X.XXX±0.010) ➤ Connector: MOLEX MINI-FIT Sr™ Header (MOLEX P/N :42819-5213) 	
B62SR24125C			

		Pin	Function Description
		1	OUTPUT -
		2	OUTPUT +
		3	INPUT -
		4	INPUT +
5	ENABLE		
		<ul style="list-style-type: none"> ➤ All dimensions in mm (inches) ➤ Tolerance: X.X±0.5 (X.XX±0.02) X.XX±0.25 (X.XXX±0.010) ➤ Connector: MOLEX MINI-FIT Sr™ Header (MOLEX P/N :42819-5213) ➤ Connector kit : Housing: 42816-0512 Terminal: 42815-0042 	
B62SR24125CC			

PHYSICAL OUTLINE

Case Size	: 190.0x76.0x44.0 mm (7.48"x2.99"x1.73")
Case Material	: Case: PC; Plate: AL6063



PART NUMBERING SYSTEM

B	62	S	R	24	125	A			C	
Form Factor	Input Voltage	Number of Outputs	Product Series	Output Voltage	Output Current	Option Code			Option Fitting	
B - Box	62 - 18V~106V	S - Single	R - Regular	24 - 24V	125 - 12.5A		With Built-in fuse holder	Enable pin	Sealed connector	Connector Kit
						A	YES	NO	NO	1xhousing+ 4 terminals
						B	YES	NO	YES	1xhousing+ 4 terminals
						C	NO	YES	NO	1xhousing+ 5 terminals

MODEL LIST

Input Voltage Range	Input		Output		EFF @48VIN 100% LOAD
B62SR24125(A\B\C)	18V~106V	14A	24.5V	12.5A	91.0%

CONTACT US:

Website: www.deltaww.com/dcdc

Email: dcdc@deltaww.com

USA:

Telephone:
East Coast: 978-656-3993
West Coast: 510-668-5100
Fax: 510-668-0680

Europe:

Telephone: +31-20-800-3900
Fax: +31-20-800-3999

Asia & the rest of world:

Telephone: +886-3-452-6107
Ext. 6221~6226
Fax: +886-3-433-1810

WARRANTY

Delta offers a two (2) years limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.